



**SHIELDTEC® STANDARD NON-DETECTABLE TAPE 3” x 1000’**

Durable, dependable non-detectable polyethylene warning tape for service and other non-critical metallic installations. Installed at proper shallow depth, ShieldTec is tough, basic protection for any type of buried cable or pipe. Suitable for open trench installation.

**INCLUDES:**

- [\(1\) SHIELDTEC® STANDARD NON-DETECTABLE TAPE \(22-126\)](#)

**FEATURES:**

- Environmentally safe
- Lead free
- Permanent messaging
- Wear resistant

**PRODUCT SPECIFICATIONS:**

Feature	Method	Value (English)	Value (SI)
Overall Thickness	ASTM D-2103	4.0 mil (Nominal)	0.1 mm (Nominal)
Weight	ASTM D-2103	17.04 lbs / 1,000 ft <sup>2</sup>	8.32 kg / 100 m <sup>2</sup>
Tensile Strength	ASTM D-882	Length: 2,565 psi	Length: 17.7 Mpa
Elongation	ASTM D-882	Length: 492%	Length: 492%
Printability	ASTM D-2578		> 40 dynes
Plastic Density	ASTM D-792-08		.951 g/cc



## SHIELDTEC® STANDARD NON-DETECTABLE TAPE 3" x 1000'

Durable, dependable non-detectable polyethylene warning tape for service and other non-critical metallic installations. Installed at proper shallow depth, ShieldTec is tough, basic protection for any type of buried cable or pipe. Suitable for open trench installation.

### INCLUDES:

[\(1\) SHIELDTEC® STANDARD NON-DETECTABLE TAPE \(22-126\)](#)

### FEATURES:

- Environmentally safe
- Lead free
- Permanent messaging
- Wear resistant

### PRODUCT SPECIFICATIONS:

Feature	Method	Value (English)	Value (SI)
Overall Thickness	ASTM D-2103	4.0 mil (Nominal)	0.1 mm (Nominal)
Weight	ASTM D-2103	17.04 lbs / 1,000 ft <sup>2</sup>	8.32 kg / 100 m <sup>2</sup>
Tensile Strength	ASTM D-882	Length: 2,565 psi	Length: 17.7 Mpa
Elongation	ASTM D-882	Length: 492%	Length: 492%
Printability	ASTM D-2578		> 40 dynes
Plastic Density	ASTM D-792-08		.951 g/cc