



SHIELDTEC® STANDARD NON-DETECTABLE TAPE 6” x 1000’

Durable, dependable non-detectable polyethylene warning tape for service and other non-critical metallic installations. Installed at proper shallow depth, ShieldTec is tough, basic protection for any type of buried cable or pipe. Suitable for open trench installation.

INCLUDES:

- [\(1\) SHIELDTEC® STANDARD NON-DETECTABLE TAPE \(22-130\)](#)

FEATURES:

- Environmentally safe
- Lead free
- Permanent messaging
- Wear resistant

PRODUCT SPECIFICATIONS:

Feature	Method	Value (English)	Value (SI)
Overall Thickness	ASTM D-2103	4.0 mil (Nominal)	0.1 mm (Nominal)
Weight	ASTM D-2103	17.04 lbs / 1,000 ft ²	8.32 kg / 100 m ²
Tensile Strength	ASTM D-882	Length: 2,565 psi	Length: 17.7 Mpa
Elongation	ASTM D-882	Length: 492%	Length: 492%
Printability	ASTM D-2578		> 40 dynes
Plastic Density	ASTM D-792-08		.951 g/cc



SHIELDTEC® STANDARD NON-DETECTABLE TAPE 6" x 1000'

Durable, dependable non-detectable polyethylene warning tape for service and other non-critical metallic installations. Installed at proper shallow depth, ShieldTec is tough, basic protection for any type of buried cable or pipe. Suitable for open trench installation.

INCLUDES:

[\(1\) SHIELDTEC® STANDARD NON-DETECTABLE TAPE \(22-130\)](#)

FEATURES:

- Environmentally safe
- Lead free
- Permanent messaging
- Wear resistant

PRODUCT SPECIFICATIONS:

Feature	Method	Value (English)	Value (SI)
Overall Thickness	ASTM D-2103	4.0 mil (Nominal)	0.1 mm (Nominal)
Weight	ASTM D-2103	17.04 lbs / 1,000 ft ²	8.32 kg / 100 m ²
Tensile Strength	ASTM D-882	Length: 2,565 psi	Length: 17.7 Mpa
Elongation	ASTM D-882	Length: 492%	Length: 492%
Printability	ASTM D-2578		> 40 dynes
Plastic Density	ASTM D-792-08		.951 g/cc