

# ADRIANA Collection

• Incandescent



## 22192UR

2-Light Wall Sconce  
Finish: Urban Rustic  
14"W x 15"H x 7.5"Ext.  
2 x 60W CA Bulbs  
Crystal Included



## 22191UR

3-Light Semi-Flush Mount  
Finish: Urban Rustic  
18"W x 11"H  
3 x 60W CA Bulbs  
Crystal Included



## 22194UR

4-Light Chandelier  
Finish: Urban Rustic  
18"W x 19"H  
4 x 60W CA Bulbs  
Crystal Included

## Conversion Kits

Conversion Kits are available to convert specified semi-flush mounts to invert bowl pendants. Included in the kit is a canopy, chain and extra loop to screw to the top of the semi-flush mount, all in matching finish.

**CKT001OI** Conversion Kit  
Oil Rubbed Bronze  
*Compatible with 5833FTOI, 5843MROI,  
5843WSOI & 10120ICOI, 10120WSOI*

**CKT001SN** Conversion Kit  
Satin Nickel  
*Compatible with 5833FTSN, 5843MRSN & 10120ICSN*

## Diffusers

Diffusers are used to conceal light clusters in pendants and wall sconces. Many of Maxim Lighting's invert bowl pendants have diffusers built in or included. Optional diffusers are also available.



**DIF001WT** Diffuser  
White  
*Compatible with 8025MRKB,  
8025MRSN and 8025WSKB*



**DIF002WT** Diffuser  
White  
*Compatible with 8026MRSN*

## Finishes

|  |                           |   |                            |
|--|---------------------------|---|----------------------------|
| <b>ABZ</b> Architectural Bronze            | <b>CR</b> Canyon Rock     | <b>NAB</b> Natural Aged Brass               | <b>SST</b> Stainless Steel |
| <b>ACP</b> Antique Copper                  | <b>CS</b> Country Stone   | <b>NB</b> Newbury Brass                     | <b>SV</b> Silver           |
| <b>AD</b> Auburn Dusk                      | <b>CT</b> Chestnut        | <b>NK</b> Nickel                            | <b>TE</b> Texture Ebony    |
| <b>AF</b> Auburn Florentine                | <b>CU</b> Colonial Umber  | <b>NW</b> Navaho White                      | <b>TW</b> Textured White   |
| <b>AL</b> Brushed Aluminum                 | <b>EG</b> Etruscan Gold   | <b>OI</b> Oil Rubbed Bronze                 | <b>TXB</b> Textured Black  |
| <b>AP</b> Antique Pecan                    | <b>FL</b> Florentine      | <b>PB</b> Polished Brass                    | <b>UB</b> Umber Bronze     |
| <b>AR</b> Anthracite                       | <b>GB</b> Greek Bronze    | <b>PB/PC</b> Polished Brass/Polished Chrome | <b>UD</b> Uddo             |
| <b>ARPN</b> Anthracite and Polished Nickel | <b>GG</b> Grecian Gold    | <b>PC</b> Polished Chrome                   | <b>UR</b> Urban Rustic     |
| <b>AT</b> Artesian Bronze                  | <b>GN</b> Golden Nior     | <b>PD</b> Platinum Dusk                     | <b>UWW</b> Umber/Wormwood  |
| <b>BF</b> Baroque Forge                    | <b>GS</b> Golden Silver   | <b>PE</b> Pewter                            | <b>WB</b> Windsor Bronze   |
| <b>BG</b> Black Gold                       | <b>GU</b> Gold Umber      | <b>PN</b> Polished Nickel                   | <b>WC</b> Weathered Copper |
| <b>BH</b> Burnt Parchment                  | <b>GY</b> Gray            | <b>PS</b> Plated Silver                     | <b>WN</b> Walnut           |
| <b>BK</b> Black                            | <b>HB</b> Heirloom Brass  | <b>PT</b> Pine Tree                         | <b>WR</b> Weathered Russet |
| <b>BR</b> Bronze Rupert                    | <b>HR</b> Heritage        | <b>RB</b> Rustic Burnished                  | <b>WT</b> White            |
| <b>BRZ</b> Anodized Bronze                 | <b>KB</b> Kentucky Bronze | <b>RC</b> Roasted Chestnut                  | <b>WW</b> Wormwood         |
| <b>BT</b> Burnish Texture                  | <b>LB</b> Luster Bronze   | <b>RE</b> Rustic Ebony                      |                            |
| <b>BZ</b> Bronze                           | <b>MB</b> Metallic Bronze | <b>SB</b> Savanna Bronze                    |                            |
| <b>CB</b> Castle Bronze                    | <b>MS</b> Matte Silver    | <b>SN</b> Satin Nickel                      |                            |
| <b>CP</b> Copper                           | <b>MW</b> Matte White     | <b>SS</b> Satin Silver                      |                            |

## Glass

|                            |                          |                         |                           |
|----------------------------|--------------------------|-------------------------|---------------------------|
| <b>AI</b> Amber Ice        | <b>FI</b> Frosted Ivory  | <b>MO</b> Mocha         | <b>TE</b> Tawny Etruscan  |
| <b>AV</b> Amber Vanilla    | <b>FL</b> Frost Lichen   | <b>MR</b> Marble        | <b>TS</b> Tawny Swirl     |
| <b>BC</b> Beveled Crystal  | <b>FM</b> Fume           | <b>MSK</b> Mirror Smoke | <b>VA</b> Vintage Amber   |
| <b>BG</b> Bubble Glass     | <b>FS</b> Frosted Seedy  | <b>NS</b> Night Shade   | <b>WC</b> Wax Candle      |
| <b>CD</b> Clear            | <b>FT</b> Frosted        | <b>PC</b> Plated Chrome | <b>WG</b> Water Glass     |
| <b>CF</b> Cafe             | <b>GF</b> Golden Frost   | <b>PS</b> Pallen Storm  | <b>WH</b> White Alabaster |
| <b>CL</b> Clear            | <b>HO</b> Honey          | <b>PV</b> Primavera     | <b>WS</b> Wilshire        |
| <b>CO</b> Cognac           | <b>IC</b> Ice            | <b>RB</b> Root Beer     | <b>WT</b> White           |
| <b>DW</b> Dusty White      | <b>JC</b> Flambe Crystal | <b>SA</b> Screen Amber  |                           |
| <b>EM</b> Ember            | <b>JF</b> Java Fog       | <b>SC</b> Stone Candle  |                           |
| <b>EV</b> Embossed Vanilla | <b>KG</b> Krackle        | <b>SR</b> Sunrise       |                           |
| <b>FC</b> Frosted Seedy    | <b>LT</b> Latte          | <b>SV</b> Soft Vanilla  |                           |
| <b>FE</b> Fiesta           | <b>MC</b> Mocha Cloud    | <b>SW</b> Satin White   |                           |

## Shades

|                        |                          |                          |                           |
|------------------------|--------------------------|--------------------------|---------------------------|
| <b>BK</b> Black        | <b>JV</b> Jave           | <b>SB</b> Shimmer Bronze | <b>TW</b> Twilight Fabric |
| <b>BS</b> Blush Fabric | <b>OF</b> Off White      | <b>ST</b> Slate Fabric   | <b>WH</b> Wheat Fabric    |
| <b>BU</b> Blue         | <b>OM</b> Oatmeal Fabric | <b>TN</b> Tan            | <b>WT</b> White           |

## Catalog Legend



**Energy Star  
Certified**

Installing new ENERGY STAR qualified light fixtures is a smart way to save energy and money. Maxim Lighting is proud to be a ENERGY STAR partner. Look for this ENERGY STAR logo to find Maxim Lighting fixtures that use 1/4 of the energy of traditional incandescent fixtures and last up to 10 times longer. More information on ENERGY STAR can be found on the ENERGY STAR web site at [energystar.gov](http://energystar.gov).



**California  
Title 24**

All new homes, additions, alterations and most commercial buildings in California must meet minimum energy efficiency standards contained in Title 24, Part 6 of the California Code of Regulations. When you see the California Title 24 symbol next to a Maxim Lighting fixtures, you can be assured that the fixtures complies. More information on California Title 24 can be found on the California Energy Commission web site at [energy.ca.gov/title24](http://energy.ca.gov/title24).



**Dimmable**

Dimmable using standard dimmer.  
Lutron® CL dimmers are recommended



**ADA Compliant**



**Energy Efficient**



**For Wet Location**



**Installs  
on Slope  
Ceiling**



**Installs  
Up or Down**



**Diffuser  
Available**



**Conversion  
Kit**



**LED**



**LED**



**LED Dimmer**