



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 222TB 1/2" Plastic Ins Bushing

*Abb Installation Products, Inc*

|                  |  |
|------------------|--|
| Catalog Number   | 222TB  |
| Manufacturer     | Abb Installation Products, Inc   |
| Description      | 1/2 Inch Non Metallic Insulated Bushing For Use With Rigid/Imc Conduit |
| Weight per unit  | 0.0090 (lbs/each)  |
| Product Category | Plastic  |

### Features

|          |              |
|----------|--------------|
| Material | Non-Metallic |
|----------|--------------|

### Dimensions and Weight

|      |          |
|------|----------|
| Size | 1/2 INCH |
|------|----------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 1/2" PLASTIC INS BUSHING   |
| extra long description | ABB 222-TB 1/2 PLASTIC INSUL. BUSHI                                    |
| Long Description       | 1/2 Inch Non Metallic Insulated Bushing for Use with Rigid/IMC Conduit |
| Product Type           | 1/2 Plastic Insul. Bushing   |

### Manufacturer Information

|                           |                 |
|---------------------------|-----------------|
| Brand                     | T&B Ind Fitting |
| GTIN                      | 00786210002224  |
| Manufacturers Part Number | 222-TB          |
| UPC                       | 786210002224    |

### Taxonomies, Classifications, and Categories

|                      |                   |
|----------------------|-------------------|
| Category Description | PVC ELBOWS        |
| Type                 | Insulated Bushing |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 100   |
| Package         | 400   |
| Weight Per each | 0.009 |

### Uses, Certifications, and Standards

|             |                                |
|-------------|--------------------------------|
| Application | For use with rigid/IMC conduit |
| standard    | UL E23018, CSA                 |