



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2334X30FT Scotch Rubber Splicing Tape, 3/4" X 30', BK Minnesota Mining (3M)

Catalog Number	2334X30FT
Manufacturer	Minnesota Mining (3M)
Description	Rubber Splicing Tape 3/4" X 30'
Weight per unit	0.2530 (lbs/each)
Product Category	Tools & Testers

### Descriptions

Description	SCOTCH RUBBER SPLICING TAPE, 3/4" X 30', BK
extra long description	3M 7000007286 Scotch® Rubber Splici
Features	Scotch® Tape 23 is a 30-mil, premium-grade, highly conformable, rubber splicing tape. The self-fusing tape has a special polyester liner, which will not stick to the tape upon unwind. It withstands temperatures up to 194 degrees F (90 degrees C). Self-fusing, ethylene propylene rubber backing and highly conformable, rubber-resin adhesive Tape measures 3/4 in x 30 ft x 30 mil Temperature rated for continuous adhesion to 194°F (90°C) Special polyester linerASTM Approved & RoHS 2002/65/EC Compliant 1 roll/c
Long Description	Rubber Splicing Tape 3/4" x 30'
Product Type	Scotch® Rubber Splicing Tape 23
Special Features	highly conformable, self-fusing Ethylene Propylene Rubber based high-insulating voltage tape

### Manufacturer Information

Brand	Scotch
GTIN	00054007150251
Manufacturers Part Number	7000007286
sub brand	Scotch
UPC	054007150251

### Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Insulating and Splicing

### Availability

Manufacturer Status	Inactive
---------------------	----------

### Packaging

Carton	20
Weight Per each	0.253