



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2334X30FT Scotch Rubber Splicing Tape, 3/4" X 30', BK *Minnesota Mining (3M)*

Catalog Number	2334X30FT
Manufacturer	Minnesota Mining (3M)
Description	Rubber Splicing Tape 3/4" X 30'
Weight per unit	0.2530 (lbs/each)
Product Category	Tools & Testers

Descriptions

Description	SCOTCH RUBBER SPLICING TAPE, 3/4" X 30', BK
extra long description	3M 7000007286 Scotch® Rubber Splici
Features	Scotch® Tape 23 is a 30-mil, premium-grade, highly conformable, rubber splicing tape. The self-fusing tape has a special polyester liner, which will not stick to the tape upon unwind. It withstands temperatures up to 194 degrees F (90 degrees C). Self-fusing, ethylene propylene rubber backing and highly conformable, rubber-resin adhesive Tape measures 3/4 in x 30 ft x 30 mil Temperature rated for continuous adhesion to 194°F (90°C) Special polyester linerASTM Approved & RoHS 2002/65/EC Compliant 1 roll/c
Long Description	Rubber Splicing Tape 3/4" x 30'
Product Type	Scotch® Rubber Splicing Tape 23
Special Features	highly conformable, self-fusing Ethylene Propylene Rubber based high-insulating voltage tape

Manufacturer Information

Brand	Scotch
GTIN	00054007150251
Manufacturers Part Number	7000007286
sub brand	Scotch
UPC	054007150251

Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Insulating and Splicing

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	20
Weight Per each	0.253