



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



242020 M12 Hackzall Recip Saw (Tool Only)

Milwaukee Electric Tool

| | |
|------------------|--|
| Catalog Number | 242020 |
| Manufacturer | Milwaukee Electric Tool |
| Description | At Only 11 In. and 2.6 LBS, The Hackzall® M12™ Cordless Lithium-Ion Reciprocating Saw Features A Compact and Light Weight Design For Superior Control and Versatility In Tight Spaces. A Powerful Motor Delivers 0-3, 000 Strokes Per Minute and A 1/2 In. Stroke Length Allows For Fast Cutting Through A Wide Range Of Material Such As Drywall, Wood, and PVC. The Variable Speed Trigger Allows For A Controlled Cut While A Quik-Lok™ Blade Clamp Offers Fast and Easy Blade Changes. |
| Weight per unit | 2.6 (lbs/each) |
| Product Category | Battery Driven Tools |

Features

| | |
|-----------------|---------|
| Battery Voltage | 12 |
| charge time | 0.5 |
| media | Yes |
| Stroke Length | 0.5 |
| Switch Type | Trigger |

Material, Color, and Finish

| | |
|------------------|-------|
| Housing Material | Metal |
|------------------|-------|

Dimensions and Weight

| | |
|--------|----|
| Height | 2 |
| Length | 11 |
| Width | 4 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | M12 HACKZALL RECIP SAW (TOOL ONLY) |
| extra long description | MILW 2420-20 12V Hackzall Saw TO |
| Features | The M12 series offers solutions that deliver portable productivity. They take on the tightest spaces and are specifically built to go anywhere. They are trade focused, system wide, lightweight with ergonomic design make portability easy, and operation faster and more productive. |
| Long Description | At only 11 in. and 2.6 lbs, the HACKZALL® M12™ cordless lithium-ion reciprocating saw features a compact and light weight design for superior control and versatility in tight spaces. A powerful motor delivers 0-3,000 strokes per minute and a 1/2 in. stroke length allows for fast cutting through a wide range of material such as drywall, wood, and PVC. The variable speed trigger allows for a controlled cut while a QUIK-LOK™ blade clamp offers fast and easy blade changes. |
| Product Type | 12V Hackzall Saw to |
| Special Features | Only 11 IN And 2.6 LB For Cutting In Tight Spaces; Keyless QUIK-LOK Blade Clamp Allows For Quick And Easy Blade Changes; All-Metal Gear Case For Added Durability; Variable Speed Trigger For Increased User Control; Battery Fuel Gauge Displays Remaining Run-Time; Accepts Both HACKZALL And SAWZALL Style Blades (See Related Products For Listing Of HACKZALL Blades); Built-In LED Light Illuminates Work Surface; SfpM: 0 - 3000 SPM; Tool Weight: 2.200 LB; Blade Clamp: QUIK-LOK Universal 1/2 IN Tang; Trigger: Varia |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242158638 |
| Manufacturers Part Number | 2420-20 |
| UPC | 045242158638 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------|
| Category Description | POWER TOOLS |
| Type | CORDLESS |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 2.64 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | For Fast Cutting Through A Wide Range Of Material Such As Drywall, Wood, And PVC |
|-------------|--|