



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 242020 M12 Hackzall Recip Saw (Tool Only)

*Milwaukee Electric Tool*

Catalog Number	242020
Manufacturer	Milwaukee Electric Tool
Description	At Only 11 In. and 2.6 LBS, The Hackzall® M12™ Cordless Lithium-Ion Reciprocating Saw Features A Compact and Light Weight Design For Superior Control and Versatility In Tight Spaces. A Powerful Motor Delivers 0-3, 000 Strokes Per Minute and A 1/2 In. Stroke Length Allows For Fast Cutting Through A Wide Range Of Material Such As Drywall, Wood, and PVC. The Variable Speed Trigger Allows For A Controlled Cut While A Quik-Lok™ Blade Clamp Offers Fast and Easy Blade Changes.
Weight per unit	2.5 (lbs/each)
Product Category	Battery Driven Tools

### Features

Battery Voltage	12
charge time	0.5
Stroke Length	0.5
Switch Type	Trigger

### Material, Color, and Finish

Housing Material	Metal
------------------	-------

### Dimensions and Weight

Height	2
Length	11
Width	4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	M12 HACKZALL RECIP SAW (TOOL ONLY)
extra long description	MILW 2420-20 12V Hackzall Saw TO
Features	M12 HACKZALL® Reciprocating Saw
Long Description	At only 11 in. and 2.6 lbs, the HACKZALL® M12™ cordless lithium-ion reciprocating saw features a compact and light weight design for superior control and versatility in tight spaces. A powerful motor delivers 0-3,000 strokes per minute and a 1/2 in. stroke length allows for fast cutting through a wide range of material such as drywall, wood, and PVC. The variable speed trigger allows for a controlled cut while a QUIK-LOK™ blade clamp offers fast and easy blade changes.
Product Type	12V Hackzall Saw to
Special Features	Only 11 IN And 2.6 LB For Cutting In Tight Spaces; Keyless QUIK-LOK Blade Clamp Allows For Quick And Easy Blade Changes; All-Metal Gear Case For Added Durability; Variable Speed Trigger For Increased User Control; Battery Fuel Gauge Displays Remaining Run-Time; Accepts Both HACKZALL And SAWZALL Style Blades (See Related Products For Listing Of HACKZALL Blades); Built-In LED Light Illuminates Work Surface; SfpM: 0 - 3000 SPM; Tool Weight: 2.200 LB; Blade Clamp: QUIK-LOK Universal 1/2 IN Tang; Trigger: Varia

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242158638
Manufacturers Part Number	2420-20
UPC	045242158638

## Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
Type	CORDLESS

## Packaging

Carton	1
Weight Per each	2.54

## Uses, Certifications, and Standards

Application	For Fast Cutting Through A Wide Range Of Material Such As Drywall, Wood, And PVC
-------------	--