

# Eaton 242410-12

Catalog Number: 242410-12

Eaton B-Line series wall mounted panel enclosure, 24" height, 10" length, 24" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series type 12 panel enclosures	242410-12
	<b>UPC</b>
	782051803204
<b>Product Length/Depth</b>	<b>Product Height</b>
10 in	24 in
<b>Product Width</b>	<b>Product Weight</b>
24 in	49.2 lb
<b>Certifications</b>	
UL 508A	
CSA C22.2.	
NEMA	



## Material/finish

### Material

Carbon steel

### Wall thickness

14 gauge

### Finish color

Painted

### Color

ANSI 61 gray

## Model

### Style

Medium single door

### Model

12 enclosure

### Cover type

Hinged

### Mounting method

Wall

### Mounting hole details

External mounting feet

### Locking provisions

Padlock provision

### Closure type

Hinged

### Special features

Plated door clamps

## Standards

### NEMA Rating

12

### Country of origin

US

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 242410-12](#)