

# Eaton 24248-4XS

Catalog Number: 24248-4XS

Eaton B-Line series wall mounted panel enclosure, 24" height, 8" length, 24" width, NEMA 4X, Hinged cover, 4XS enclosure, Wall mount, Medium single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	24248-4XS
	UPC
	782051407563

Product Length/Depth	Product Height
8 in	24 in

Product Width	Product Weight
24 in	49 lb

## Certifications

UL 50  
CSA C22.2.  
NEMA

## defaultTaxonomyAttributeLabel

### Country of origin

US

### Special features

Stainless door clamps

### Style

Medium single door

### Finish color

#4 brushed

### Color

Gray

### NEMA Rating

4X

### Cover type

Hinged

### Wall thickness

14 gauge

### Material

304 stainless steel

### Model

4XS enclosure

### Mounting method

Wall

### Closure type

Hinged

### Locking provisions

Padlock provision

### Mounting hole details

External mounting feet

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 24248-4XS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)