

Eaton 24248 RTSCGV NK

Catalog Number: 24248 RTSCGV NK

Eaton B-Line series Type 3/3R junction boxes, 24" height, 8" length, 24" width, NEMA 3R, Screw cover, RTSCGV NK enclosure, Surface mounted, Medium single door, No knockout, Embossed thru holes, Galvanized steel

General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series Type 3/3R junction boxes	24248 RTSCGV NK
	UPC
	782051007572
Product Length/Depth	Product Height
8 in	24 in
Product Width	Product Weight
24 in	44.5 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

Material/finish

Material

Galvanized steel

Wall thickness

14 gauge

Finish color

Unfinished

Color

Gray

Model

Style

Medium single door

Model

RTSCGV NK enclosure

Cover type

Screw

Mounting method

Surface

Mounting hole details

Embossed thru holes

Special features

Rainhood,embossed mounting provisions,platedscrews

Standards

NEMA Rating

3R

Country of origin

US

Resources

Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

Specifications and datasheets

[Eaton Specification Sheet - 24248 RTSCGV NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)