

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301460079](#)  
**Status:** **Active**  
**Overview:** [Watertite® Wet-Location Wiring Solutions](#)  
**Description:** Watertite Plug with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V, Cord Grip Body Size F2

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA	LR6837
UL	E10176

**General**

Product Family	Wiring Devices
Series	<a href="#">130146</a>
IP Rating	IP67
NEMA Configuration	NEMA L7-15
Overview	<a href="#">Watertite® Wet-Location Wiring Solutions</a>
Product Literature Order No	987650-8067
Product Name	Watertite
Receptacle Type	N/A
Specialty	N/A
Type	Plug
UPC	78678871204
Woodhead	Yes

**Physical**

Cord Grip Body Size	F2 1/2"
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Locking Blade	Yes
Poles	2-pole/3-wire

**Electrical**

Cord Type	N/A
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	277V

**Material Info**

Engineering Number	24W34
--------------------	-------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
------------	--------------

ELV	Not Relevant
-----	--------------

RoHS Phthalates	Not Reviewed
-----------------	--------------

**Search Parts in this Series**

[130146 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301460079](#)  
**Status:** **Active**  
**Overview:** [Watertite® Wet-Location Wiring Solutions](#)  
**Description:** Watertite Plug with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V, Cord Grip Body Size F2

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA	LR6837
UL	E10176

**General**

Product Family	Wiring Devices
Series	<a href="#">130146</a>
IP Rating	IP67
NEMA Configuration	NEMA L7-15
Overview	<a href="#">Watertite® Wet-Location Wiring Solutions</a>
Product Literature Order No	987650-8067
Product Name	Watertite
Receptacle Type	N/A
Specialty	N/A
Type	Plug
UPC	78678871204
Woodhead	Yes

**Physical**

Cord Grip Body Size	F2 1/2"
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Locking Blade	Yes
Poles	2-pole/3-wire

**Electrical**

Cord Type	N/A
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	277V

**Material Info**

Engineering Number	24W34
--------------------	-------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[130146 Series](#)