



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



251I 3/4" Ins Steel Emt Compression Connector

Bridgeport Fittings

Catalog Number	251I
Manufacturer	Bridgeport Fittings
Description	Emt Compression Connector, 3/4 In Trade Size, Straight Connection Orientation, Zinc Electro-Plated, Insulated, 1-27/32 In Length, 1-5/16 In Diameter, +105 °C Operating Temperature, 0.0007 LB/Ea
Weight per unit	0.0007 (lbs/each)
Product Category	Steel Insulated Straight Compr

Features

Connector Type	Compression
insulation	Insulated Throat
Material	Steel
media	Yes

Material, Color, and Finish

Finish	Zinc Electroplated
--------	--------------------

Dimensions and Weight

Size	3/4
------	-----

Descriptions

Description	3/4" INS STEEL EMT COMPRESSION CONNECTOR
extra long description	BPT 251-I 3/4" COMP. CONN. INS. STE

Manufacturer Information

Brand	Bridgeport
GTIN	00781747102515
UPC	781747102515

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	CONNECTOR

Packaging

Carton	25
Package	250
Weight Per each	0.0007

Uses, Certifications, and Standards

Application	Used to join EMT to box or enclosure. Concrete tight.
standard	cULus
Temperature Rating	105?°C