



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



252020 M12 Fuel Hackzall Recip Saw (Tool Only)

Milwaukee Electric Tool

Catalog Number	252020
Manufacturer	Milwaukee Electric Tool
Description	The M12 Fuel™ Hackzall® Is The Fastest Cutting and Most Powerful Saw In Its Class, Delivering Over 4X More Run-Time, Up to 70% Faster Cutting, and Up to 6X Longer Tool Life Than Competitive Saws.
Weight per unit	3.6 (lbs/each)
Product Category	Battery Driven Tools

Features

Battery Voltage	12
Stroke Length	0.625
Switch Type	Trigger

Material, Color, and Finish

Housing Material	Plastic with Rubber Overmold
------------------	------------------------------

Dimensions and Weight

Length	11
Width	2.75

Descriptions

Description	M12 FUEL HACKZALL RECIP SAW (TOOL ONLY)
extra long description	MILW 2520-20 M12 FUEL™ HACKZALL® -
Features	M12 FUEL™ HACKZALL® Reciprocating Saw
Long Description	The M12 FUEL™ HACKZALL® is the fastest cutting and most powerful saw in its class, delivering over 4X more run-time, up to 70% faster cutting, and up to 6X longer tool life than competitive saws.
Product Type	M12 Fuel™ Hackzall® - Tool Only

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242318827
Manufacturers Part Number	2520-20
UPC	045242318827

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
----------------------	-------------

Packaging

Carton	1
Weight Per each	3.61