



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 253DCI2 1-1/4" Diecast Emt Insulated Concrete Tight Conn

*Bridgeport Fittings*

Catalog Number	253DCI2
Manufacturer	Bridgeport Fittings
Description	Connector, Compression, Zinc Die Cast, 105 Degree C Insulated Throat, Size 1 1/4 Inch
Weight per unit	0.4170 (lbs/each)
Product Category	Die Cast Insulated Straight CO

### Features

Connector Type	Compression
insulation	Insulated Throat
Material	Zinc Die Cast
media	Yes

### Material, Color, and Finish

Finish	Ball burnish
--------	--------------

### Dimensions and Weight

Size	1 1/4
------	-------

### Descriptions

Description	1-1/4" DIECAST EMT INSULATED CONCRETE TIGHT CONN
extra long description	BPT 253-DCI2 1 1/4" COMP. CONN. INS
Features	Think Orange: Zinc Advantage –Error-free Performance – meets same stringent UL tests as steel. Bridgeport zinc EMT fittings set the standard for EMT.
Long Description	Connector, Compression, Zinc Die Cast, 105 Degree C Insulated Throat, Size 1 1/4 Inch
Product Type	1 1/4" Comp. Conn. Ins.
Special Features	Concrete-Tight

### Manufacturer Information

Brand	Bridgeport
GTIN	00781747162533
Manufacturers Part Number	253-DCI2
UPC	781747162533

### Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	CONNECTOR

### Trade Size

Trade Size	1-1/4
------------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	10
Package	100
Weight Per each	0.417

## Uses, Certifications, and Standards

Application	Used to join steel EMT to box or enclosure. Concrete-tight. 1/2" thru 2" suitable for use with Steel or Aluminum EMT. Insulator rated 105degree C.
standard	UL, CSA
Temperature Rating	105°C