



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



26342RED Deco Duplex Recept 20A 125V S-Wire RD

Pass & Seymour/Legrand

Catalog Number	26342RED
Manufacturer	Pass & Seymour/Legrand
Description	Heavy-Duty Decorator Spec Grade Duplex Receptacle Side Wire 20A 125V
Weight per unit	0.1948 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Outlet Type	Commercial, Indoor
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Material, Color, and Finish

Color	Red
-------	-----

Dimensions and Weight

Height	3.813
Width	.833



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	DECO DUPLEX RECP 20A 125V S-WIRE RD
extra long description	P&S 26342RED DECO DUP RECEP 20A 125
Long Description	Heavy-Duty Decorator Spec Grade Duplex Receptacle Side Wire 20A 125V
Product Type	Deco Dup Recep 20A 125V S-Wire Red
Special Features	Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body. One-piece, brass, triple-wipe power contacts for lasting retention. Heavy-duty compact design for easier installation and long lasting performance. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face. Terminal compartments isolated from each other for positive conductor containment. Side wire accepts #14 - #10 AWG solid or stranded w

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007785234
Manufacturers Part Number	26342-RED
UPC	785007785234

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.1948

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	FEDSPEC, CULUS, UL498, cUL CSA
Temperature Rating	-40° - 60° C