



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



26352GRY Deco Duplex Recept 20A 125V B+S Wire Gry *Pass & Seymour/Legrand*

Catalog Number	26352GRY
Manufacturer	Pass & Seymour/Legrand
Description	Heavy-Duty Decorator Spec Grade Duplex Receptacle Back and Side Wire 20A 125V
Weight per unit	0.2050 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Outlet Type	Indoor, Commercial
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Height	3.813
Width	.833



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	DECO DUPLEX RECP 20A 125V B+S WIRE GRY
extra long description	P&S 26352GRY DECO DUP RECEP 20A 125
Long Description	Heavy-Duty Decorator Spec Grade Duplex Receptacle Back and Side Wire 20A 125V
Product Type	Deco Dup Recep 20A 125V B+S Wire Gry
Special Features	Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body. One-piece, brass, triple-wipe power contacts for lasting retention. Heavy-duty compact design for easier installation and long lasting performance. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face. Terminal compartments isolated from each other for positive conductor containment. Side and internal screw-pressure-plate back wire ac

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007785371
Manufacturers Part Number	26352-GRY
UPC	785007785371

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	10
Package	100
Weight Per each	0.205

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	FEDSPEC, CULUS, UL498, cUL CSA, FEDSPEC