



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 267RT 3" Diecast Emt Raintight Compression Coupling

*Bridgeport Fittings*

Catalog Number	267RT
Manufacturer	Bridgeport Fittings
Description	3" Raintight Coupling
Weight per unit	2.2 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

Connector Type	Compression
media	Yes
outside diameter	4.08

### Dimensions and Weight

Length	101.6000;4.0000000000000000
--------	-----------------------------

### Descriptions

Description	3" DIECAST EMT RAIN TIGHT COMPRESSION COUPLING
extra long description	BPT 267-RT 3" RAIN TIGHT CPLG
Features	Think Orange: Quality In, Water Out. Listed for Damp or Wet Locations.
Long Description	3" Raintight Coupling
Product Type	3" Raintight CPLG
Special Features	With Bridgeport's newly redesigned Raintight Compression Couplings, 266-RT through 269-RT, contractors can install just one wet location fitting for either thread less Rigid / IMC or EMT.

### Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747142672
Manufacturers Part Number	267RT
UPC	781747142672

### Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	Raintight

### Trade Size

Trade Size	3
------------	---

### Packaging

Carton	12
Weight Per each	2.208



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

These 3" dual Listed Zinc Alloy fittings come standard with a 105° C temperature rated insulated throat and the words "Rigid / EMT and RAIN TIGHT" clearly cast into the body. This marking helps the AHJ to precisely confirm the products intended use. Patented

standard

cULus