

Eaton 271B-BOX

Catalog Number: 271B-BOX

Eaton commercial grade combination switch, Stand, #14 - #12 AWG, 15A, Commer, 120/277V, bk and sd wiring, togg, Maint closure, Screw, Brass, Brown, -20-60°C, (2) 1-pole, dplx, thermoplas



General specifications

Product Name	Catalog Number
Eaton commercial grade combination switch	271B-BOX
	UPC
	032664160301
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
1.08 in	0.215 lb
Compliances	Certifications
RoHS Compliant	NOM
	cULus Listed

Product specifications

Connector type

Screw

Switch type

(2) single-pole

Configuration

(2) toggle

Closure type

Maintained

Color

Brown

Wiring method

Back and side

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Number Of Poles

Single-pole

Contact type

Brass

Type

Standard

Device grade

Commercial

Style type

Duplex

Operating temperature

-20 to 60 °C

Voltage rating

120/277 V

Resources

Catalogs

[Residential Buyers Guide B-16](#)

Specifications and datasheets

[Eaton Specification Sheet - 271B-BOX](#)

Application

Commercial

Torque rating

14 lbf-inch

Actuator

Toggle



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia