

Eaton 276V-BOX

Catalog Number: 276V-BOX

Eaton commercial grade combination switch, Stand, #14 - #12 AWG, 15A, Commer, 120/277V, bk and sd wiring, togg, Maint closure, Screw, Brass, Ivy, -20-60°C, (2) 3-way, dplx, thermoplas



General specifications

Product Name	Catalog Number
Eaton commercial grade combination switch	276V-BOX
	UPC
	032664161506
Product Length/Depth	Product Height
4.38 in	1.88 in
Product Width	Product Weight
1.75 in	0.2 lb
Compliances	Certifications
RoHS Compliant	cULus Listed
	NOM

Product specifications

Connector type

Screw

Switch type

(2) Three-way

Configuration

(2) toggle

Closure type

Maintained

Color

Ivory

Wiring method

Back and side

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Contact type

Brass

Type

Standard

Device grade

Commercial

Style type

Duplex

Operating temperature

-20 to 60 °C

Number of ways

(2) Three-way

Voltage rating

120/277 V

Application

Resources

Catalogs

[Arrow Hart Buyers Guide Section E](#)

Specifications and datasheets

[Eaton Specification Sheet - 276V-BOX](#)

Commercial

Torque rating

14 lbf-inch

Actuator

Toggle



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia