

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470059](#)  
**Status:** **Active**  
**Overview:** [Watertite® Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L16-20, 3Ø 480V, Cord Grip Body Size F3

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                        E10176

**General**

Product Family                      Wiring Devices  
 Series                                  [130147](#)  
 IP Rating                                IP67  
 NEMA Configuration                NEMA L16-20  
 Overview                               [Watertite® Wet-Location Wiring Solutions](#)  
 Product Literature Order No        987650-8067  
 Product Name                         Watertite  
 Receptacle Type                      Single  
 Specialty                                N/A  
 Type                                      Connector  
 UPC                                        78678871315  
 Woodhead                                Yes

**Physical**

Cord Grip Body Size                 F3 3/4"  
 Flange                                  No  
 Flip Lid                                 No  
 Gender                                 Female  
 Length                                 N/A  
 Locking Blade                         Yes  
 Net Weight                            367.409/g  
 Poles                                     3-pole/4-wire

**Electrical**

Cord Type                                N/A  
 Current - Maximum per Contact    20.0A  
 GFCI                                     No  
 Lighted Connector                    No  
 Voltage - Maximum                  3Ø 480V

**Material Info**

Engineering Number                 27W76



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130147 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470059](#)  
**Status:** **Active**  
**Overview:** [Watertite® Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L16-20, 3ø 480V, Cord Grip Body Size F3

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837  
 UL      E10176

**General**

Product Family      Wiring Devices  
 Series      [130147](#)  
 IP Rating      IP67  
 NEMA Configuration      NEMA L16-20  
 Overview      [Watertite® Wet-Location Wiring Solutions](#)  
 Product Literature Order No      987650-8067  
 Product Name      Watertite  
 Receptacle Type      Single  
 Specialty      N/A  
 Type      Connector  
 UPC      78678871315  
 Woodhead      Yes

**Physical**

Cord Grip Body Size      F3 3/4"  
 Flange      No  
 Flip Lid      No  
 Gender      Female  
 Length      N/A  
 Locking Blade      Yes  
 Net Weight      367.409/g  
 Poles      3-pole/4-wire

**Electrical**

Cord Type      N/A  
 Current - Maximum per Contact      20.0A  
 GFCI      No  
 Lighted Connector      No  
 Voltage - Maximum      3ø 480V

**Material Info**

Engineering Number      27W76



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[130147 Series](#)