

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301420036](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Super-Safeway Plug with Locking Blade, 3 Pole/4 Wire, NEMA L14-30, 125V/250V

Documents:
[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification	
CSA	LR6837
UL	E10176
General	
Product Family	Wiring Devices
Series	130142
IP Rating	N/A
NEMA Configuration	NEMA L14-30
Overview	Heavy-Duty Industrial Wiring Devices
Product Literature Order No	987650-8068
Product Name	Super-Safeway
Receptacle Type	N/A
Specialty	N/A
Type	Plug
UPC	78678870435
Woodhead	Yes
Physical	
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Locking Blade	Yes
Poles	3-pole/4-wire
Electrical	
Cord Type	N/A
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V / 250V
Material Info	
Engineering Number	2874



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130142](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301420036](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Super-Safeway Plug with Locking Blade, 3 Pole/4 Wire, NEMA L14-30, 125V/250V

Documents:
[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification	
CSA	LR6837
UL	E10176
General	
Product Family	Wiring Devices
Series	130142
IP Rating	N/A
NEMA Configuration	NEMA L14-30
Overview	Heavy-Duty Industrial Wiring Devices
Product Literature Order No	987650-8068
Product Name	Super-Safeway
Receptacle Type	N/A
Specialty	N/A
Type	Plug
UPC	78678870435
Woodhead	Yes
Physical	
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Locking Blade	Yes
Poles	3-pole/4-wire
Electrical	
Cord Type	N/A
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V / 250V
Material Info	
Engineering Number	2874



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130142](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION