



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



29W75 Tlconn IP67 30A 3PH 250V L1530R

Pass & Seymour/LeGrand

Catalog Number	29W75
Manufacturer	Pass & Seymour/LeGrand
Description	Locking Watertight Connector, 30AMP 3 250VOLT, Nema Configuration L15-30, Multipoint Sealing System Provides Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated.
Weight per unit	0.8300 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
Cord Type	12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max
Material	Rubber
Number of Wires	4
Phase	3
Poles	3
Voltage Rating	250
Wire Size	12 - 6

Descriptions

Description	TLCONN IP67 30A 3PH 250V L1530R
extra long description	P&S 29W75 TLCONN IP67 30A 3PH 250V
Long Description	Locking Watertight Connector, 30amp 3 250volt, NEMA Configuration L15-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.
Product Type	Tlconn IP67 30A 3PH 250V L1530R
Special Features	Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007033496
Manufacturers Part Number	29W75
UPC	785007033496

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Locking Connector



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.83

Uses, Certifications, and Standards

Application	High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings Ideal for washdown areas — rated wa
environmental conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized
nema rating	L15-30R
standard	UL Listed, CSA Listed