

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470108](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V, Cord Grip Body Size F4

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                        E10176

**General**

Product Family                      Wiring Devices  
 Series                                  [130147](#)  
 Exclude SD Check                      Yes  
 IP Rating                                IP67  
 NEMA Configuration                      NEMA L16-30  
 Overview                                [Watertite Wet-Location Wiring Solutions](#)  
 Product Literature Order No              987650-8067  
 Product Name                              Watertite  
 Receptacle Type                          Single  
 Specialty                                 N/A  
 Type                                        Connector  
 UPC                                         78678871334

**Physical**

Cord Grip Body Size                      F4 1"  
 Flange                                      No  
 Flip Lid                                      No  
 Gender                                        Female  
 Length                                        N/A  
 Locking Blade                                Yes  
 Net Weight                                  441.798/g  
 Poles                                         3-pole/4-wire

**Electrical**

Cord Type                                      N/A  
 Current - Maximum per Contact              30.0A  
 GFCI    No  
 Lighted Connector                              No  
 Voltage - Maximum                              3Ø 480V

**Material Info**

Engineering Number                          29W76



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130147](#) Series

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470108](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V, Cord Grip Body Size F4

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR6837  
UL E10176

**General**

Product Family Wiring Devices  
 Series [130147](#)  
 Exclude SD Check Yes  
 IP Rating IP67  
 NEMA Configuration NEMA L16-30  
 Overview [Watertite Wet-Location Wiring Solutions](#)  
 Product Literature Order No 987650-8067  
 Product Name Watertite  
 Receptacle Type Single  
 Specialty N/A  
 Type Connector  
 UPC 78678871334

**Physical**

Cord Grip Body Size F4 1"  
 Flange No  
 Flip Lid No  
 Gender Female  
 Length N/A  
 Locking Blade Yes  
 Net Weight 441.798/g  
 Poles 3-pole/4-wire

**Electrical**

Cord Type N/A  
 Current - Maximum per Contact 30.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 3Ø 480V

**Material Info**

Engineering Number 29W76



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130147](#) Series