



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10917 Mill Creek Rd
66219-0000, KS Lenexa
Phone: 913-563-7000
Fax: 913-563-7050



29W77 Turnlok Conn IP67 4W 30A 600V L1730R

Pass & Seymour/Legrand

Catalog Number	29W77
Manufacturer	Pass & Seymour/Legrand
Description	Locking Watertight Connector, 30AMP 3Y 600VOLT, Nema Configuration L17-30, Multipoint Sealing System Provides Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated.
Weight per unit	0.8300 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
Cord Type	12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max
indoor/outdoor	Both
ip rating	IP67
Material	Rubber
Number of Phases	1.0
Number of Wires	4.0
Phase	Single
Poles	3-way
Voltage	600.0 V
Voltage Rating	600
Wire Size	12 - 6 AWG

Material, Color, and Finish

Color	Yellow
-------	--------

Descriptions

Description	TURNLOK CONN IP67 4W 30A 600V L1730R
extra long description	P&S 29W77 TL CONN IP67 4W 30A 600V
Features	Watertight
Long Description	Locking Watertight Connector, 30amp 3Y 600volt, NEMA Configuration L17-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.
Product Type	TL Conn IP67 4W 30A 600V L1730R
Special Features	Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10917 Mill Creek Rd
66219-0000, KS Lenexa
Phone: 913-563-7000
Fax: 913-563-7050

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007033731
Manufacturers Part Number	29W77
UPC	785007033731

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	CONNECTOR

Trade Size

Amperage	30.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.83

Uses, Certifications, and Standards

Application	High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings Ideal for washdown areas — rated wa
environmental conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized
nema rating	NEMA 4X, NEMA 6P
Operating Temperature	-40°-60°C
standard	UL Listed, CSA Listed