

Red•Dot® metallic weatherproof covers

Technical Specifications



Applications :

- Protects receptacles, switches, and plugs for single gang and two gang configurations in dry and wet locations
- Provides a lockable cover that complies with OSHA lockout/tagout requirements
- Prevents accidental equipment disconnects, reduces tampering, and deters theft and equipment removal

Features/Benefits :

- Alloy A360 copper-free (less than 0.004 copper content) aluminum provides increased corrosion resistance
- Die cast, metal construction provides long lasting durability
- NEMA 3R rating ensures protection against falling rain, sleet, and external ice formation when used with appropriate device boxes
- Clear UL and CSA markings speed approval by inspectors
- Wide range of cover depths and receptacle configurations accommodate almost every common plug and cord size
- Combination box or device mounting design provides flexibility in installation

Standard Materials :

- Covers and Plates: Die cast aluminum alloy A360
- Gaskets: Closed-cell foam


Standard Finish :

- Powder coated finish

Compliances :

Compliances as noted on each page of the catalogue in clude:

- CSA Certified
- UL Listed



Red•Dot® metallic weatherproof covers



Duplex



GFCI




Single Receptacle



Switch



Cat. No.	Description
Single Gang Cover – 2-1/4 in. Internal Depth (Aluminum)	
CKSUU	Small vertical cover universal code keeper accommodates duplex, GFCI, single receptacle and toggle switch – lockable



Duplex




GFCI



Single Receptacle



Switch



Duplex



GFCI



Single Receptacle




Switch



Cat. No.	Description
Single Gang Cover – 3-1/4 in. Internal Depth (Aluminum)	
CKMU	Medium horizontal cover universal code keeper accommodates duplex, GFCI, single receptacle and toggle switch – lockable
CKMUV	Medium vertical cover universal code keeper accommodates duplex, GFCI, single receptacle and toggle switch – lockable


Red•Dot® metallic weatherproof covers




Single Receptacle




Cat. No.	Description
Single Gang Cover – 4-3/4 in. Internal Depth (Aluminum)	
CKLSVU	Large vertical cover – Box mount universal code keeper with adapter rings to accommodate 1-19/32 in. and 1-3/4 in. single receptacles – lockable



Two duplex receptacle




Single and GFCI receptacle




Duplex and GFCI receptacle




Toggle and duplex receptacle



Two GFCI receptacle




Toggle and GFCI receptacle




Two single receptacle



Toggle and single receptacle



Single and duplex receptacle



Toggle and single receptacle



Cat. No.	Description
Two Gang Cover – 4-1/4 in. Internal Depth (Aluminum)	
2CKU*	Regular cover universal code keeper accommodates various configurations – lockable

* Can be used to cover one receptacle with an oversized wall opening

Red•Dot® metallic weatherproof covers

Technical Specifications



Applications :

- Protects receptacles, switches, and plugs for single gang and two gang configurations in dry and wet locations
- Provides a lockable cover that complies with OSHA lockout/tagout requirements
- Prevents accidental equipment disconnects, reduces tampering, and deters theft and equipment removal

Features/Benefits :

- Alloy A360 copper-free (less than 0.004 copper content) aluminum provides increased corrosion resistance
- Die cast, metal construction provides long lasting durability
- NEMA 3R rating ensures protection against falling rain, sleet, and external ice formation when used with appropriate device boxes
- Clear UL and CSA markings speed approval by inspectors
- Wide range of cover depths and receptacle configurations accommodate almost every common plug and cord size
- Combination box or device mounting design provides flexibility in installation

Standard Materials :

- Covers and Plates: Die cast aluminum alloy A360
- Gaskets: Closed-cell foam


Standard Finish :

- Powder coated finish

Compliances :

Compliances as noted on each page of the catalogue in clude:

- CSA Certified
- UL Listed



Red•Dot® metallic weatherproof covers



Duplex



GFCI




Single Receptacle



Switch



Cat. No.	Description
Single Gang Cover – 2-1/4 in. Internal Depth (Aluminum)	
CKSUU	Small vertical cover universal code keeper accommodates duplex, GFCI, single receptacle and toggle switch – lockable



Duplex




GFCI



Single Receptacle



Switch



Duplex



GFCI



Single Receptacle




Switch



Cat. No.	Description
Single Gang Cover – 3-1/4 in. Internal Depth (Aluminum)	
CKMU	Medium horizontal cover universal code keeper accommodates duplex, GFCI, single receptacle and toggle switch – lockable
CKMUV	Medium vertical cover universal code keeper accommodates duplex, GFCI, single receptacle and toggle switch – lockable


Red•Dot® metallic weatherproof covers




Single Receptacle




Cat. No.	Description
Single Gang Cover – 4-3/4 in. Internal Depth (Aluminum)	
CKLSVU	Large vertical cover – Box mount universal code keeper with adapter rings to accommodate 1-19/32 in. and 1-3/4 in. single receptacles – lockable



Two duplex receptacle




Single and GFCI receptacle




Duplex and GFCI receptacle




Toggle and duplex receptacle



Two GFCI receptacle




Toggle and GFCI receptacle




Two single receptacle



Toggle and single receptacle



Single and duplex receptacle



Toggle and single receptacle



Cat. No.	Description
Two Gang Cover – 4-1/4 in. Internal Depth (Aluminum)	
2CKU*	Regular cover universal code keeper accommodates various configurations – lockable

* Can be used to cover one receptacle with an oversized wall opening