












CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET QTY	NJ	IL	TX	CA	GA
----------------	-------------	----------	--------	----------	------------	----	----	----	----	----

## Paralux III High Performance


### EP3GAX Series

	<b>2'x2' - 9 Cell</b>											
	AP32U	2 U-LAMP, 2'X2' STATIC PARABOLIC, 9 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	080083520176	16.1	1	32				★		
	2EP3GAVX-2U6T8S33I-UNV-EB81-U	2 U-LAMP, 2'X2' AIR SUPPLY PARABOLIC, W/VANES, 9 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8	080083520220	14.3	1	40	•	•			★	
	2EP3GX-2U6T8S33I-UNV-EB81-U	2 U-LAMP, 2'X2' STATIC PARABOLIC, 9 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8	080083520145	14.3	1	36	•	•	•	•	•	★
	2EP3GX-317S33I-UNV-EB81-U	3 LAMP, 2'X2' STATIC PARABOLIC, 9 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8	080083520084	14.3	1	40		•			★	

	<b>2'x4' - 12 Cell</b>										
	2EP3GX-232S26I-UNV-EB81-U	2 LAMP, 2'X4' STATIC PARABOLIC, 12 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8	080083520169	27.36	1	20				•	★

	<b>2'x4' - 18 Cell</b>												
	AP3	3 LAMP, 2'X4' AIR SUPPLY PARABOLIC W/VANES, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	622696199785	27.36	1	16				•	★		
	2EP3GAVX-332S36I-UNV-EB81-U	3 LAMP, 2'X4' AIR SUPPLY PARABOLIC, W/VANES, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8	662401000685	27.36	1	20	•	•			•	★	
	2EP3GAX-332S36I-UNV-EB81-U	3 LAMP, 2'X4' AIR SUPPLY PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8	662401339785	27.36	1	20					•	★	
	2EP3GX-232S36I-UNV-EB81-U	2 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8	080083520237	27.36	1	20					•	★	
	2EP3GX-332S36I-UNV-EB81-U	3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8	662401012084	27.36	1	20	•	•	•	•	•	★	
	2EP3GX-332S36I-UNV-EB82-U	3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, TWO - CEE LISTED ELECTRONIC BALLAST, T8	662401339761	27.36	1	20		•	•	•	•	★	
	2EP3GX-332S36I-UNV-L8735-A3/8-2/18G-EB81-U	3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8, W/LAMPS & FLEX	662401339730	27.36	1	20		•			•	★	
	2EP3GX-332S36I-UNV-L8735-EB81-U	3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS	662400201908	27.36	1	20	•	•	•			★	
	2EP3GX-332S36I-UNV-L8741-EB81-U	3 LAMP, 2'X4' STATIC PARABOLIC, 18 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS	622697478087	27.36	1	20					•	★	

	<b>2'x4' - 32 Cell</b>											
	2EP3GX-432S48I-UNV-EB81-U	4 LAMP, 2'X4' STATIC PARABOLIC, 32 CELL, SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS	080083520206	27.36	1	20				•	★	

	<b>Chicago Approved - 2'x2' 9 Cell</b>										
	ATW-SW4-2EP3GAVX-2U6T8S33I-UNV-EB81-U	2 U-LAMP, 2'X2' AIR SUPPLY PARABOLIC W/VANES, 9 CELL SEMI SPECULAR/LOW IRIDESCENT HAZE 3" LOUVER, ELECTRONIC BALLAST, T8, CHICAGO PLENUM APPROVED	623961053474	16.47	1	32		•			★

## Parabolic Surface High Performance

### Standard 3" Parabolic

EP3X-S36I-24-C-U	REPLACEMENT LOUVER, 2EP3, 18 CELL, SEMI-SPECULAR, 2'X4'	080083684380	6.2	1	20					•	★	
------------------	---	--------------	-----	---	----	--	--	--	--	---	---	--

★ Indicates ARRA Eligible Product   **E** Indicates EISA Compliant Pulse Start Products    Indicates Off the Shelf Product