



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

2RB14

2RB14 16-14 Nylon Ins Butt Splice

Abb Installation Products, Inc

Catalog Number	2RB14
Manufacturer	Abb Installation Products, Inc
Description	Nylon-Insulated Butt Splice, Length 1.19 Inches, Width .21 Inches, Maximum Insulation Diameter .148, Wire Range #16-#14 Awg, Color Blue, Copper, Tin Plated
Weight per unit	0.0040 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Material	Copper
Voltage Rating	600 V

Material, Color, and Finish

Color	Blue
Finish	Electro -Tin Plated

Descriptions

Description	16-14 NYLON INS BUTT SPLICE
extra long description	ABB 2RB14 INS NYLON BUTT SPLICE 16-
Long Description	Nylon-Insulated Butt Splice, Length 1.19 Inches, Width .21 Inches, Maximum Insulation Diameter .148, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated
Product Type	Ins Nylon Butt Splice 16-14 Awg
Special Features	Nylon insulated splices meet or exceed the requirements of MIL-T-7928. These splices are color-coded according to wire size

Manufacturer Information

Brand	Sta-Kon
GTIN	00786210800202
Manufacturers Part Number	2RB14
UPC	786210800202

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Nylon Insulated Butt Splice

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Weight Per each	0.004



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard	UL E9809 / UL E9809
Temperature Rating	105 C