

MECHANICAL CONNECTORS

Aluminum Dual Rated Splicer/Reducers

SR SERIES



FEATURES

- For splicing two copper or aluminum wires of equal or different sizes.
- Made of 6061T-6 aluminum alloy.
- Electro-tin plated for low contact resistance.

All dimensional data is listed in inches.

CAT. NO.	FIG. NO.	WIRE RANGE
2SR	1	2-14 AWG
1/OSR	1	1/0-14 AWG
4/OSR	1	4/0-6 AWG
250SR	2	250 MCM-6 AWG
350SR	2	350 MCM-6 AWG
500SR	2	500 MCM-3/0 AWG
750SR	2	750-250 MCM

RATINGS



LISTED
WIRE CONNECTOR

UL 486A/B Listed.

TEMPERATURE RATING:

90 °C.

VOLTAGE:

600V (2000V max. per UL486B).





TORQUE VALUE (IN./LBS.)	WRENCH SIZE	LENGTH (L)	WIDTH (W)	HEIGHT (H)	STD. CTN. QTY.
50	Slotted	1.594	0.443	0.550	50
120	Slotted	1.500	0.530	0.630	25
250	5/16	2.310	0.812	1.000	24
330	5/16	4.094	0.812	1.000	10
400	3/8	4.190	1.130	1.190	8
550	3/8	5.000	1.380	1.500	3
550	3/8	6.250	1.630	1.750	3

