



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30076 Wiretwist Wire Connector, WT6 Red, 100/Box

Ideal

| | |
|------------------|--|
| Catalog Number | 30076 |
| Manufacturer | Ideal |
| Description | Ideal, Wire Connector, Wire-Nut, Twist-On, Number Of Conductors: 1 to 6, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Conductor Range: 18 - 12 Awg, Min 2-18 Max 4-14 W/ 1-18, Material: Flame-Retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Model Number: 76B, Flammability Rating: UI 94V-2 |
| Weight per unit | 0.9100 (lbs/each) |
| Product Category | Electrical Fixture Conn (Nuts |

Features

| | |
|----------------|-------------------------------|
| Material | Flame-retardant Polypropelene |
| Voltage Rating | 600 |

Material, Color, and Finish

| | |
|-------|-----|
| Color | Red |
|-------|-----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | WIRETWIST WIRE CONNECTOR, WT6 RED, 100/BOX |
| extra long description | IDEAL 30-076 WIRENUT 76B RED, 100 B |
| Features | The IDEAL Wire-Nut Wire Connector set new standards for innovation, quality and convenience when it was first introduced in 1928. As the first screw-on wire connector in America, it literally set the industry standard for years to come. With a fixed, square-wire spring and a positive grip shell, the Wire-Nut is perfect to twist-on with fingers for a secure connection that will last. The refined wire range makes it the best choice for fine stranded wire applications. The Wire-Nut also features a tough, flame |
| Long Description | IDEAL, Wire Connector, Wire-Nut, Twist-On, Number Of Conductors: 1 to 6, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Conductor Range: 18 - 12 AWG, Min 2-18 MAX 4-14 w/ 1-18, Material: Flame-retardant polypropelene, Color: Red, Voltage Rating: 600 V, Model Number: 76B, Flammability Rating: UL 94V-2 |
| Product Type | Wirenut 76B Red, 100 BX |
| Special Features | Comply With Federal Specification W-S-610E;Deep Skirt Helps Protect Against Flash-Over;Features: Fixed, Square-Wire Spring Creates Its Own Threads Maintains A Secure Positive Grip That Will Not Relax Over Time;Flammability Rating: UL 94V-2;Model Number: 76B;No Pre-Twisting Required Positive Grip Design Provides Fast, Easy Installation;Reusable For Easy Circuit Changes And Additions;Tough, UL94V-2 Flame-Retardant Shell Rated At 105 Degree C (221 Degree F);UL Listed To 486C And CSA Certified To C22.2 #188 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250300761 |
| Manufacturers Part Number | 30-076 |
| UPC | 783250300761 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
| Type | Twist-On |

Packaging

| | |
|-----------------|------|
| Carton | 100 |
| Package | 1000 |
| Weight Per each | 0.91 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Insulating or Joining 2 or more conductors |
| environmental conditions | Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F) |
| standard | CSA Certified to C22.2 #188, UL Listed to 486C, complies with Federal Specification W-S-610E |