
ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1755 Bee Creek Rd
Branson, MO 65616-0000
Phone: 4172430209
Fax: 0000000000



301033J IN-SURE PUSH-IN WIRE CONN, 33 3-PORT ORG, 250/JAR

IDEAL

Catalog Number	301033J
Manufacturer	IDEAL
Description	Push-In Wire Connector, Orange Insulation Color, +221 °F Operating Temperature, 0.780 in Overall Length, 0.690 in Overall Width, 0.380 in Overall Height, 600 V (Building Wire);1000 V (Maximum Signs/Lighting Fixture), 0.01 lb
Weight per unit	1.5 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Voltage Rating	600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures
Wire Size	#12 AWG - #20 AWG Solid, #12 AWG - #16 AWG (19 Strand Or Less) #18 AWG (7 Strand) Stranded, #14 AWG - #18 AWG (19 Strand Or Less) Stranded (Tin Bonded)
Wire Type	Solid, Stranded, Stranded (Tin Bonded)
Connection	3 Ports

Material, Color, and Finish

Color	Orange

Dimensions and Weight

Size	0.780 IN Length X 0.690 IN Width X 0.380 IN Height

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1755 Bee Creek Rd
Branson, MO 65616-0000
Phone: 4172430209
Fax: 0000000000

Descriptions

Description	IN-SURE PUSH-IN WIRE CONN, 33 3-PORT ORG, 250/JAR
Features	Ergonomic design for easy grip and comfortable installationLow insertion force for fast and easy connectionsCompact size makes installation easyClear shell gives visual verification of connectionTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)Approved for bonding and grounding applicationsStrip, push, connect – the fastest way to make a connection.The In-Sure Push-In Wire Connector is perfect for residential, light commercial, lighting retrofit, and pre-fab wiring systems, or any other branch c
Long Description	IDEAL, Wire Connector, In-Sure, Push-In, Size: 0.780 IN Length X 0.690 IN Width X 0.380 IN Height, Connection: 3 Ports, Wire Size: #12 AWG - #20 AWG Solid, #12 AWG - #16 AWG (19 Strand Or Less) #18 AWG (7 Strand) Stranded, #14 AWG - #18 AWG (19 Strand Or Less) Stranded (Tin Bonded), Color: Orange, Voltage Rating: 600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures, Temperature Rating: 105 DEG C Shell Rated, Wire Type: Solid, Stranded, Stranded (Tin Bonded), Model: 33
Product Type	Push-In 12AWG 3-Port, 250 Jar
Special Features	Features: No-Twist Connection Reduces Repetitive Motion Fatigue; Low Insertion Force For Fast And Easy Connections; Compact Size Makes Installation Easy; Clear Shell Gives Visual Verification Of Connection; UL Listed To 486C And CSA Certified To C22.2 #188; UL 467 Listed For Grounding And Bonding Applications; 600V Maximum Building Wire, 1000V; Maximum Signs And Lighting Fixtures; Shell Rated To 105 DEG C; Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F); Model: 33
Extra Long Description	IDEAL 30-1033J PUSH-IN 12AWG 3-PORT

Manufacturer Information

Brand	Ideal
	Ideal Industries
GTIN	00783250693559
UPC	783250

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Push-In

Availability

Minimum Qty	250

1755 Bee Creek Rd
Branson, MO 65616-0000
Phone: 4172430209
Fax: 0000000000

Packaging

Carton	250
Package	1500
Weight Per Each	1.5 (lbs/each)

Uses, Certifications, and Standards

Application	For Grounding And Bonding Applications
Temperature Rating	105 DEG C Shell Rated
Standard	CSA C22.2 #188, 486C/467 UL Listed, RoHS