



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



301042 Spliceline In-Line Wire Conn, 42 Orange, 100/Box

Ideal

| | |
|------------------|---|
| Catalog Number | 301042 |
| Manufacturer | Ideal |
| Description | Ideal, Wire Connector, Spliceline, In-Line, Wire Size: 12 Awg - 20 Awg Solid, 12 Awg - 16 Awg Stranded, Color: Orange, Voltage Rating: 600 V, Amperage Rating: 20 Amp, Temperature Rating: 105 Deg C, Wire Type: Solid, Stranded, Model: 42 |
| Weight per unit | 0.0040 (lbs/each) |
| Product Category | Utp Connectors |

Features

| | |
|-----------------|---|
| amperage rating | 20 |
| Voltage Rating | 600 |
| Wire Size | 12 AWG - 20 AWG Solid, 12 AWG - 16 AWG Stranded |
| Wire Type | SOLID, STRANDED |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Orange |
|-------|--------|

Descriptions

| | |
|------------------------|---|
| Description | SPLICELINE IN-LINE WIRE CONN, 42 ORANGE, 100/BOX |
| extra long description | IDEAL 30-1042 SPLICELINE 42 ORANGE, |
| Features | A faster alternative to the butt splice.The SpliceLine In-Line Wire Connector is a revolutionary in-line wire connector that utilizes patented push-in technology in a unique design to provide a crimp-free, solderless butt splice faster and easier. The 2-port model supports a wide range of either stranded or solid wires, allowing one connector to cover the same range as three traditional butt splices and installs two times faster than a traditional butt splice.The end-to-end connection of SpliceLine is a gr |
| Long Description | IDEAL, Wire Connector, SpliceLine, In-Line, Wire Size: 12 AWG - 20 AWG Solid, 12 AWG - 16 AWG Stranded, Color: Orange, Voltage Rating: 600 V, Amperage Rating: 20 AMP, Temperature Rating: 105 DEG C, Wire Type: Solid, Stranded, Model: 42 |
| Product Type | Spliceline 42 Orange, 100 Box |
| Special Features | Features: Crimp-Free, Push-In Butt Splice; Low Insertion Force For Fast Connections; Easily Passes Through 1/2" Knockouts; End-To-End Connection Ideal For Pre-Fab Operations; Transparent Polycarbonate Window For Visual Inspection Of Connection; Wide Wire Range Of 12 - 20 Awg Solid, 12 - 16 Awg Stranded; Made In The U.S.A.; Model: 42 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250709090 |
| Manufacturers Part Number | 301042 |
| UPC | 783250709090 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------|
| Category Description | WIRE NUTS |
| Type | In-Line |

Availability

| | |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 100 |
| Package | 1000 |
| Weight Per each | 0.004 |

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Application | For Fast Connections And Pre-Fab Operations And Visual Inspection Of Connection |
| standard | CSA C22.2 #188, 486C/467 UL Listed, RoHS |
| Temperature Rating | 105 DEG C |