



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30454 Wing-Nut Wire Conn, Model 454 Blue, 25/Box

Ideal

Catalog Number	30454
Manufacturer	Ideal
Description	Twist-On Wingnut, Insulated, Blue Insulation Color, +221 °F Operating Temperature, 1 to 6 Conductors, 600 V Ac, 0.02 LB
Weight per unit	0.5000 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant polypropelene shell
Voltage Rating	600

Material, Color, and Finish

Color	Blue
-------	------

Descriptions

Description	WING-NUT WIRE CONN, MODEL 454 BLUE, 25/BOX
extra long description	IDEAL 30-454 WINGNUT 454 BLUE, 25 B
Features	Largest range in the Industry - from 2 #18 to up 4 #10High-leverage, contoured wing provides superior torque on every twistWide range, live-action spring handles small combinations and expands to accommodate large combinations as you need itCopolymer shell expands for smooth, progressive tightening providing dependable connectionsRemovable for repeat usage on same size or larger combinationsMore power with every twist.The Wing-Nut Wire Connector provides an easy, secure grip when connecting a wide range of

Manufacturer Information

Brand	Ideal
GTIN	00783250304547
UPC	783250304547

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Twist-On

Availability

minimum qty	25
-------------	----

Packaging

Carton	25
Package	250
Weight Per each	0.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Insulating or Joining 2 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA Certified to C22.2 #188, UL Listed to 486C, complies with Federal Specification W-S-610E, RoHS Compliant