

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

320 SW 28TH ST 72712-0000, AR Bentonville Phone: 479-250-1930 Fax: 479-250-1931



30654 Wing-Nut Wire Conn, Model 454 Blue, 100/Bag Ideal

30654		
Ideal		
Ideal, Wire Connector, Wing-Nut, Twist-On, Number Of Conductors: 1 to 6, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Conductor Range: 14 - 6 Awg, Min 3 - 12, Max 1-6 W/2-8, Material: Flame-Retardant Polypropelene Shell, Color: Blue, Voltage Rating: 600 V, Model Number: 454, Flammability Rating: UL94V-2		
0.0190 (lbs/each)		
Electrical Fixture Conn (Nuts		
Flame-retardant polypropelene shell		
Yes		
600		
Blue		



ELLIOTT ELECTRIC SUPPLY 320 SW 28TH ST 72712-0000, AR Bentonville Phone: 479-250-1930 Fax: 479-250-1931

_	•		
11000	rin	TIA	nc
Desc			
-			

Description	WING-NUT WIRE CONN, MODEL 454 BLUE, 100/BAG		
extra long description	IDEAL 30-654 WINGNUT 454 BLUE, 100		
Features	Largest range in the Industry - from 2 #18 to up 4 #10High-leverage, contoured wing provides superior torque on every twistWide range, live-action spring handles small combinations and expands to accommodate large combinations as you need itCopolymer shell expands for smooth, progressive tightening providing dependable connectionsRemovable for repeat usage on same size or larger combinationsMore power with every twist.The Wing-Nut Wire Connector provides an easy, secure grip when connecting a wide range of		
Long Description	IDEAL, Wire Connector, Wing-Nut, Twist-On, Number Of Conductors: 1 to 6, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Conductor Range: 14 - 6 AWG, Min 3 - 12, MAX 1-6 w/2-8, Material: Flame-retardant polypropelene shell, Color: Blue, Voltage Rating: 600 V, Model Number: 454, Flammability Rating: UL94V-2		
Product Type	Wingnut 454 Blue, 100 Bag		
Special Features	Comply With Federal Specification W-S-610E;Deep skirt helps protect against flash-over and turned-back strands for maximum dielectric protection;Features: Specially designed contour wings provide a secure grip for extra levarage;Flammability Rating: UL94V-2;Live action Spring expands to accept wire shape abd size with no pre-twisting required;Model Number: 454;Square wire spring threads directly onto conductors for fast, secure connections;Togh UL 94V-2 flame-retardent shell rated at 105 deg c(221 deg F);U		

Brand	Ideal	
GTIN	00783250306541	
Manufacturers Part Number	30-654	
UPC	783250306541	

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Туре	Twist-On

Packaging

3 3		
Carton	100	
Package	1000	
Weight Per each		



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

320 SW 28TH ST 72712-0000, AR Bentonville Phone: 479-250-1930 Fax: 479-250-1931

Uses, Certifications, and Standards

Application	Insulating or Joining 2 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA Certified to C22.2 #188, UL Listed to 486C, complies with Federal Specification W-S-610E, RoHS Compliant