

# VARI-BIT® STEP DRILL BITS

## Drills Fast, Clean, Round Holes



### LENOX® VARI-BIT® Kits



**4 Piece (1/8"–1")**  
**Product No.**  
**30926-VBK-4**  
 4 sizes: VB1, VB2, VB7,  
 VB8. Instruction sheet.  
 Plastic case.



**4 Piece (1/8"–1-3/8")**  
**Product No.**  
**30929-30/929**  
 4 sizes: VB1, VB3, VB8,  
 VB12. Instruction sheet.  
 Plastic case.



**4 Piece (3/16"–1-1/8")**  
**Product No.**  
**30928-VBKE**  
 4 sizes: VB3, VB6, VB8,  
 VB11. Instruction sheet.  
 Plastic case.



**6 Piece (1/8"–1-1/8")**  
**Product No.**  
**30927-VBKA-6**  
 6 sizes: VB1, VB2, VB6,  
 VB7, VB8, VB11.  
 Instruction sheet.  
 Plastic case.



**3 Piece (1/8"–1")**  
**Product No.**  
**30889-889**  
 3 sizes: VB1, VB2, VB3.  
 Instruction sheet.  
 Plastic case.

### THE LENOX® ADVANTAGE™

- **Accurate, burr-free holes**  
Patented two flute design cuts fast, clean, round holes.
- **Starts on contact**  
Split point design for faster penetration and less walking.
- **Long tool life**  
Steam oxide coating adds durability. Enhanced flute design removes chips rapidly, ensuring longer tool life.

### Specifications (1 per pack)

U.S. PATENT NO. 4582458

Product Number	Photo	Hole Sizes (Inches)	Chuck Size (Inches)	Unibit®	Klein Unibit®
30881-VB1		1/8, 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 13/32, 7/16, 15/32, 1/2	1/4	1	1-59001
30882-VB2		1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1	3/8	20	2-59002
30883-VB3		1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4	3/8	3	3-59003
30884-VB4		3/16, 1/4, 5/16, 3/8, 7/16, 1/2	1/4	2	5-59005
30886-VB6		3/8, 1/2	1/4	10, 12*	7-59007
30887-VB7		7/8 (for 1/2" conduit)	3/8	11	8-59008
30908-VB8		3/16, 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8	3/8	4	14-590014
30909-VB9		7/8, 1-1/8, 1-7/32	3/8	11, 13, 14	59011
30888-VB11		7/8, 1-1/8 (for 1/2" and 3/4" conduit)	3/8	13**	11-590011
30912-VB12		7/8, 1-1/8, 1-7/32, 1-1/4, 1-3/8	3/8	none	none
30925-VBX8		Extension 8" Fits 3/8" drill chuck & larger. 1 per clam			

\* LENOX® VARI-BIT® #6 combines Unibit® #10 & #12.

\*\* Unibit® #13 has 1-1/8" step only. VARI-BIT® has both 7/8" & 1-1/8".