






**TCP Item Number: 31054850**      Lamp code: F54T5HO/850



Cathode Guarded

Average Rated Life (hours)  
 3 hours per start ----- 24,000

TCLP Compliant ----- Yes  
 Low Mercury ----- Yes

### Physical Characteristics

Lamp type ----- T5  
 Base type ----- Miniature Bipin  
 Lamp Material ----- Soda Lime  
 Phosphor ----- Tri-Phosphor

Lamp Diameter (inches)  
 Nominal (D) ----- .625  
 Maximum (D) ----- .670

Overall Length (inches)  
 Nominal (C) ----- 45.2  
 Maximum (C) ----- 45.8

Face to End of opposing pin (inches)  
 Maximum (B) ----- 45.52  
 Minimum (B) ----- 45.42


### Photometric Characteristics

Initial Lumens ----- 5000  
 Mean Lumens (40% of rated life) ----- 4750  
 Correlated Color Temperature (Kelvin) ----- 5000  
 Color Rendering Index (CRI) ----- 85  
 Normal Efficacy (Lumens/Watts) ----- 92.6


### Electrical Characteristics

Lamp Watts ----- 54  
 Nominal Lamp Volts ----- 118  
 Nominal Lamp Operating Frequency (Hz) -- 50-60 Hz  
 Min. Starting Temperature (°C) ----- -20  
 Min. Starting Lamp Voltage at 10°C ----- 520  
 Min. Cathode Resistance (Rh/Rc) ----- 4.25  
 Max. Cathode Resistance (Rh/Rc) ----- 6.5


### Spectral Power Distribution



### Lamp Lumen Maintenance



### Typical Lamp Mortality



**24** MONTH STANDARD WARRANTY

For the most up-to-date specs, please visit [www.tcp.com](http://www.tcp.com)

\*Testing performed with Instant Start Ballast.

