



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



31365 Yellow 77, 55-Gallon Drum

Ideal

| | |
|------------------|--|
| Catalog Number | 31365 |
| Manufacturer | Ideal |
| Description | Yellow 77 Lubricant, Size: 55 Gal, Container: Drum, Specific Gravity: 0.98, Plastic Safe: Yes, Slight Perfume Odor, Voc: 2.7 GPL (As Packaged, Minus Water), Working Temperature: 40 - 100 Deg F, Boiling Point: 212 Deg F (100 Deg C), Percent Volatile By Volume: Less Than 90 PCT, Percent Solid By Weight: Approximately 20 PCT, Yellow Paste, 7 - 8.5 PH, Solubility In Water: Moderate, Storage Temperature: 32 - 130 Deg F, UI Listed, For Wire Pulling |
| Weight per unit | 505.0 (lbs/each) |
| Product Category | Paint, Chemicals, Etc. |

Features

| | |
|------------------|----------------|
| odor | Slight Perfume |
| specific gravity | 0.98 |

Dimensions and Weight

| | |
|------|----|
| Size | 55 |
|------|----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | YELLOW 77, 55-GALLON DRUM |
| extra long description | IDEAL 31-365 YELLOW 77 55 GALLON DR |
| Features | IDEAL Yellow 77 Wire pulling lubricant is a wax-based formula, and is the perfect general purpose lube. It is safe to use with most cable types except low-density polyethylene and semi-conducting jackets. It won't break down/separate after repeated exposure to freezing temperatures and dries to a thin, non-conductive film that won't clog conduit. Yellow 77 has a creamy texture and clings to cable throughout long pulls. Apply conveniently and uniformly by hand or brush. It is a homogeneous blend that requir |
| Long Description | Yellow 77 Lubricant, Size: 55 GAL, Container: Drum, Specific Gravity: 0.98, Plastic Safe: Yes, Slight Perfume Odor, Voc: 2.7 GPL (As Packaged, Minus Water), Working Temperature: 40 - 100 DEG F, Boiling Point: 212 DEG F (100 DEG C), Percent Volatile By Volume: Less Than 90 PCT, Percent Solid By Weight: Approximately 20 PCT, Yellow Paste, 7 - 8.5 pH, Solubility In Water: Moderate, Storage Temperature: 32 - 130 DEG F, UI Listed, For Wire Pulling |
| Product Type | Yellow 77 55 Gallon Drum |
| Special Features | The #1 brand of wire pulling lubricant since 1959 - the perfect general purpose lube; Wax-based formula provides superior lubricity; Safe to use with most cable types except low-density polyethylene and semi-conducting jackets; Won't break down or separate after repeated exposure to freezing temperatures; Dries to a thin, non-conductive film that won't clog conduit; Clings to cable throughout long pulls; Easy to apply by hand or with pump; Creamy texture applies easily and uniformly; Homogeneous blend requ |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250313655 |
| Manufacturers Part Number | 31-365 |
| UPC | 783250313655 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | WIRE LUBE, MARKERS, & TIES |
| Type | Lubricant |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 505 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|------------------------|
| Application | For Wire Pulling |
| standard | UL Listed |