

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301360033](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway Multi-Tap (3) Outlet Box with Buss Bars, NEMA 5-15

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family Power Distribution
 Series [130136](#)
 Enclosure Rating N/A
 GFCI Reset N/A
 Mounting Style Portable
 Open Neutral Relay N/A
 Overview [Outlet Boxes](#)
 Product Literature Order No 987650-7737
 Product Name Super-Safeway
 Receptacle Type Triple
 Type Multi-Tap and Strip Cordset
 UPC 78678875077
 Woodhead Yes

Physical

Cord Diameter 8.26-16.64mm (.325-.655")
 Cord Grip Body Size Double C-Clamp
 Cord Length N/A
 Feed-Thru No
 Flip Lid No
 Material - Housing Rubber
 Net Weight 1093.157/g
 Number of Receptacles 3
 Packaging Type Carton

Electrical

Cord Type N/A
 Current - Maximum per Contact 15.0A
 GFCI No
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-15
 Voltage - Maximum 120V

Material Info

Engineering Number 31593



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130136](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301360033](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway Multi-Tap (3) Outlet Box with Buss Bars, NEMA 5-15

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family Power Distribution
 Series [130136](#)
 Enclosure Rating N/A
 GFCI Reset N/A
 Mounting Style Portable
 Open Neutral Relay N/A
 Overview [Outlet Boxes](#)
 Product Literature Order No 987650-7737
 Product Name Super-Safeway
 Receptacle Type Triple
 Type Multi-Tap and Strip Cordset
 UPC 78678875077
 Woodhead Yes

Physical

Cord Diameter 8.26-16.64mm (.325-.655")
 Cord Grip Body Size Double C-Clamp
 Cord Length N/A
 Feed-Thru No
 Flip Lid No
 Material - Housing Rubber
 Net Weight 1093.157/g
 Number of Receptacles 3
 Packaging Type Carton

Electrical

Cord Type N/A
 Current - Maximum per Contact 15.0A
 GFCI No
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-15
 Voltage - Maximum 120V

Material Info

Engineering Number 31593



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130136](#) Series