

Compact Fluorescent PL Lamp | 10,000 Hours average rated life

Applications:

Perfect for most commercial applications: Use where a standard incandescent is used.

- + Table Lamps
- + Wall Sconces
- + Recessed Downlighting
- + Ceiling Fixtures
- + Outdoor Fixtures
- + Ceiling Fans



NOT compatible with dimming applications

Special Application Options: (Ordering Suffix)


- 2700°K (27K), 3000°K (30K), 3500°K (35K), 4100°K (41K), 5000°K (50K)

Features and Benefits


- Long Life, 10,000 hour average rated life
- Lower maintenance and labor costs for lamp replacements
- Lasts 7 years, based on 3 hours use a day
- Bulb lasts 10-13 times longer than similar incandescent bulbs
- 82 CRI




G23 base
Twin Tube




2GX7 base
Twin Tube




G23-2 base
Quad Tube




G24d base
Quad Tube



GX32d base
Quad Tube



G24q base
Quad Tube



GX24q base
Triple Tube



PL Lamp Specifications

Item #	Description	Initial Lumens	CCT	M.O.L. (inches)	Diameter (inches)
32007					
32007	7W TWIN TUBE PL LAMP 2PIN 27K	400	2700	5.30	1.22
3200741K	7W TWIN TUBE PL LAMP 2PIN 41K	400	4100	5.30	1.22
32009					
32009	9W TWIN TUBE PL LAMP 27K	570	2700	6.50	1.01
3200935K	9W TWIN TUBE PL LAMP 35K	570	3500	6.50	1.01
3200941K	9W TWIN TUBE PL LAMP 41K	570	4100	6.50	1.01
32013					
32013	13W TWIN TUBE PL LMP 2-PIN 27K	780	2700	7.00	1.06
3201335K	13W TWIN TUBE PL LMP 2-PIN-35K	780	3500	7.00	1.06
3201341K	13W TWIN TUBE 41K	780	4100	7.00	1.06
3201350K	13W TWIN TUBE PL LMP 2-PIN 50K	730	5000	7.00	1.06
324132GX7					
324132GX7	13W 4 PIN PL 2GX7 BASE	780	2700	6.375	1.26
324132GX735K	13W 4 PIN PL 2GX7 BASE 35K	780	3500	6.375	1.26
32018Q					
32018Q	18W QUAD PL LMP-2700K	1150	2700	5.96	1.34
32018Q35K	18W QUAD PL LMP-35K	1150	3500	5.96	1.34
32018Q41K	18W QUAD PL LMP-41K	1150	4100	5.96	1.34
32026Q					
32026Q	26W QUAD PL LMP-27K	1680	2700	6.75	1.34
32026Q35K	26W QUAD PL LMP-35K	1680	3500	6.75	1.34
32026Q41K	26W QUAD PL LMP-41K	1680	4100	6.75	1.34
32413Q					
32413Q	13W QUAD LAMP PL 4-PIN	860	2700	5.08	1.03
32413Q35K	13W QUAD LAMP PL 4-PIN 35K	860	3500	5.08	1.03
32413Q41K	13W QUAD LAMP PL 4-PIN 41K	860	4100	5.08	1.03
32418Q					
32418Q	18W QUAD LAMP PL 4-PIN	1150	2700	5.60	1.02
32418Q30K	18W QUAD LAMP PL 4-PIN 30K	1150	3000	5.60	1.02
32418Q35K	18W QUAD LAMP PL 4-PIN 35K	1150	3500	5.60	1.02
32418Q41K	18W QUAD LAMP PL 4-PIN 41K	1150	4100	5.60	1.02
32426Q					
32426Q	26W QUAD LAMP PL 4-PIN	1700	2700	6.25	1.04
32426Q30K	26W QUAD LAMP PL 4-PIN 30K	1700	3000	6.25	1.04
32426Q35K	26W QUAD LAMP PL 4-PIN 35K	1700	3500	6.25	1.04
32426Q41K	26W QUAD LAMP PL 4-PIN 41K	1700	4100	6.25	1.04
32418T					
32418T	18W TRIPLE LAMP PL 4-PIN 27K	1200	2700	4.28	1.75
32418T30K	18W TRIPLE LAMP PL 4-PIN 30K	1200	3000	4.28	1.75
32418T35K	18W TRIPLE LAMP PL 4-PIN 35K	1200	3500	4.28	1.75
32418T41K	18W TRIPLE LAMP PL 4-PIN 41K	1200	4100	4.28	1.75
32426T					
32426T	26W TRIPLE LAMP PL 4-PIN 27K	1680	2700	4.87	1.50
32426T30K	26W TRIPLE LAMP PL 4-PIN 30K	1680	3000	4.87	1.50
32426T35K	26W TRIPLE LAMP PL 4-PIN 35K	1680	3500	4.87	1.50
32426T41K	26W TRIPLE LAMP PL 4-PIN 41K	1680	4100	4.87	1.50
32426T50K	26W TRIPLE LAMP PL 4-PIN 50K	1580	5000	4.87	1.50
32432T					
32432T	32W TRIPLE LAMP PL 4-PIN 27K	1950	2700	5.46	1.47
32432T30K	32W TRIPLE LAMP PL 4-PIN 30K	1950	3000	5.46	1.47
32432T35K	32W TRIPLE LAMP PL 4-PIN 35K	1950	3500	5.46	1.47
32432T41K	32W TRIPLE LAMP PL 4-PIN 41K	1950	4100	5.46	1.47
32432T50K	32W TRIPLE LAMP PL 4-PIN 50K	1800	5000	5.46	1.47
32442T					
32442T	42W TRIPLE LAMP PL 4-PIN 27K	2550	2700	6.26	1.48
32442T30K	42W TRIPLE LAMP PL 4-PIN 30K	2550	3000	6.26	1.48
32442T35K	42W TRIPLE LAMP PL 4-PIN 35K	2550	3500	6.26	1.48
32442T41K	42W TRIPLE LAMP PL 4-PIN 41K	2550	4100	6.26	1.48
32442T50K	42W TRIPLE LAMP PL 4-PIN 50K	2400	5000	6.26	1.48

12 MONTH WARRANTY