



15A/125V TRADEMASTER® DUPLEX RECEPTACLE, BROWN

3232 | [Pass & Seymour](#)

FEATURES & BENEFITS

Our Pass & Seymour TradeMaster® receptacles combine a traditional look with reliable, time-tested operation for any residential application.



PRODUCT
ENVIRONMENTAL PROFILE

- High-impact resistant thermoplastic construction.
- Extra-long strap. Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier #12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 - #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Low profile face.
- Traditional contoured face.
- (3232 models) Self-grounding models provide automatic ground clip.

SPECIFICATIONS

GENERAL INFO

Color: Brown
Type: Duplex
Number Of Poles: 2

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
cULus: Yes

UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): .960"
Height (US): 3.31"
Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
NEMA Rating: Yes
Volts: 125
Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: No