

TradeMaster Receptacle

3232W



Duplex Grounding Receptacle with high-impact resistant thermoplastic construction. It has ultrasonic welding of face to back body and long-term blade retention. 15 amp, 125 volt. White.

features & benefits

- Extra-long strap. Quickloop wire looping aid. Longer tri-drive screws for easier #12 AWG looping.
- Extra-large circuit break-off tabs. Side-access push wire release. Side wire accepts #12 - #14 AWG solid wire. Push wire accepts #14 AWG solid only. Low profile face. Traditional contoured face.
- (3232 models) Self-grounding models provide automatic ground clip.

specifications

General Info

Color: White
Number Of Poles: 2
Number Of Wires: 3

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
Federal Spec: No
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406

Dimensions

Depth U S: 0.96"
Height U S: 3.31"
Width U S: 1.32"

Technical Information

Amps: 15
Volts: 125
Volts A C: 125

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No