



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



328 3" Plastic Bushing *Bridgeport Fittings*

| | |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | 328 |
| Manufacturer | Bridgeport Fittings |
| Description | Plastic Bushing, 3 In Trade Size, Gray, Insulated, Straight Connection Orientation, Threaded Connection, 3-13/16 In Width, 3/4 In Height, 3-13/16 In Diameter, +150 °C Operating Temperature, 0.0839 LB/Ea |
| Weight per unit | 0.0839 (lbs/each) |
| Product Category | Plastic |

Features

| | |
|----------|---------|
| Material | Plastic |
| media | Yes |

Material, Color, and Finish

| | |
|--------|-----------|
| Color | Gray |
| Finish | NO FINISH |

Dimensions and Weight

| | |
|------|---|
| Size | 3 |
|------|---|

Descriptions

| | |
|------------------------|----------------------------------|
| Description | 3" PLASTIC BUSHING |
| extra long description | BPT 328 3" PLASTIC BUSHING 105 C |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747003287 |
| UPC | 781747003287 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------------------------|
| Category Description | COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS |
| Type | BUSHING |

Trade Size

| | |
|------------|---|
| Trade Size | 3 |
|------------|---|

Packaging

| | |
|-----------------|--------|
| Carton | 25 |
| Weight Per each | 0.0839 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Used with locknut to terminate threaded rigid and IMC to box, or used with connector to prevent damage to wire insulation. Rated 105 degree C.

standard

UL

Temperature Rating

105°C