

Products

- > [Index](#)
- > [Featured Products](#)
- > [Cross Reference](#)
- > [UPC Search](#)

Product Datasheet

[Catalog Home](#) [Home Page](#)

[Search](#)

3404 -- Straight Liquidtight Connector 1" Trade Size



Product Specifications

Family	Liquidtight Conduit and Cord Connectors
Fittings Classification	Steel / Malleable Iron - Straight Connectors
Sub Class	Uninsulated
Trade Size	1"
Standard Packaging	Carton
Ship Carton Length	5.8750
Ship Carton Width	4.500
Ship Carton Height	4.00
WT. PER HU.	37.00
Dimension A	1-15/16"
Dimension B	19/32"
Thread Spec. B	1-11-1/2 NPT
Dimension C	2-3/16"
Unit Carton Quantity	10
Ship Carton Quantity	10
UPC Number	050169034040

Applications

- For use in outdoor or indoor locations on flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Use to positively bond the conduit to a box or enclosure
- RACO® liquidtight connectors are suitable for use in Class 1, Division 2; Class 2, Division 1 and 2; and Class 3, Division 1 and 2 hazardous locations

Product Features

- Patented split gland-ring is designed to slip onto the conduit quickly and to grip the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts
- All components are reusable -- RACO® liquidtight connectors may be easily disassembled and reused after years of service
- Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening
- Heavy duty locknut included with every RACO® liquidtight connector assures continuity of ground
- All metallic components are zinc electro plated for added corrosion protection
- Bodies - 3/8" to 1" Steel ; 1-1/4" to 4" Malleable Iron ; •Nuts - 3/8" to 1" Steel ; 1-1/4" to 4" Malleable Iron

Compliances

UL CSA

