



# 1 in. 90 Degree Liquidtight Connector, Uninsulated

By Raco  
Catalog # 3424



1 in. 90 Degree Liquidtight Connector, Uninsulated

\*Representative Image

## Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

## General

Conduit Type	Liquidtight
EU RoHS Indicator	Yes
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel/Malleable Iron
UPC	050169034248

## Dimensions

Dimensions	3.25 in x 1.719 in x 2.9 in
Height	2.9 in
Length	3.25 in
Trade Size	1 in
Weight	0.585 lb
Width	1.719 in

## Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3150

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - LT COND](#)  
[Sales Drawings - 3424](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - RACO: Liquidtight Connectors vs. popular competitor](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-3424-SPEC-EN | REV 5/2024