



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 35096 Twist-A-Nut Conduit Deburring Head Only, Slot Tip

*Ideal*

Catalog Number	35096
Manufacturer	Ideal
Description	Ideal, Conduit Deburring Tool Head, Twist-A-Nut, Slotted Tip, Warranty: Lifetime Guarantee
Weight per unit	0.3500 (lbs/each)
Product Category	Hand Tool Bits, Parts, Acessor

### Descriptions

Description	TWIST-A-NUT CONDUIT DEBURRING HEAD ONLY, SLOT TIP
extra long description	IDEAL 35-096 CONDUIT DEBURR HEAD W
Features	Deburs inside and outside edges of 1/2 in., 3/4 in. and 1 in. thin wall conduit Hooded tip tightens EMT fitting set screws without slipping Square tip "seats" much more quickly on fitting screws than slotted version Head removes and is interchangeable with IDEAL 7-in-1 Twist-a-Nut Screwdriver shaft (#35-908) Head can be used at low speed setting in drill or cordless screwdriver The Twist-a-Nut Conduit deburring tool head is used with IDEAL 7-in-1 Twist -a-Nut screwdriver shaft to smooth inside/outside edges of
Long Description	IDEAL, Conduit Deburring Tool Head, Twist-A-Nut, Slotted Tip, Warranty: Lifetime Guarantee
Product Type	Conduit Deburr Head W Slot Tip
Special Features	Features: Deburs Inside And Outside Edges Of 1/2, 3/4, And 1 IN Thin Wall Conduit; Hooded Tip Tightens Emt Fitting Set Screws Without Slipping; Removable Head Interchangeable With Ideal 7-In-1 Twist -A-Nut Screwdriver Shaft (35-908); Head Can Be Used In Drill Or Cordless Screwdriver; Universal Wire-Nut Wrench In Handle End Eases Installation Of Twist-On Connectors; Lifetime Guarantee (Excludes Blades); Warranty: Lifetime Guarantee

### Manufacturer Information

Brand	Ideal
GTIN	00783250583225
Manufacturers Part Number	35-096
UPC	783250583225

### Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	SLOTTED TIP

### Packaging

Carton	1
Weight Per each	0.35