



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 35203 Number 2 Phillips Speed Driver

*Ideal*

Catalog Number	35203
Manufacturer	Ideal
Description	Ideal, Screwdriver, Quick-Rotating, Phillips Head, Tip Size: 3/16 In, Overall Length: 9-3/4 In, Shank Length: 6 In, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Blade Finish: Nickel-Chrome Plating, Tip Type: Phillips, Shank Size: 3/16 In
Weight per unit	0.3500 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

### Features

Handle Type	Cushioned Rubber Grip
Shank Length	6
Tip Size	3/16
tip type	Phillips

### Material, Color, and Finish

Blade Material	Chrome Vanadium Steel
----------------	-----------------------

### Dimensions and Weight

Overall Length	9-3/4
----------------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	NUMBER 2 PHILLIPS SPEED DRIVER
extra long description	IDEAL 35-203 Screwdriver, Ideal, Quic
Features	The Cabinet Quick Rotating Screwdriver is ideal for threading screws in switches, fixtures and anchors. For quick and easy use, it provides one-handed crank action. It has shank diameter that matches blade tip for tough applications and features a cross-ground tip to provide a precise and secure fit in the screw slot. Plate chipping is prevented by a vapor-blasted tip, and the screwdriver's nickel-chrome plating offers corrosion resistance and a smooth feel. The Cabinet Quick Rotating Screwdriver also feat
Long Description	IDEAL, Screwdriver, Quick-Rotating, Phillips Head, Tip Size: 3/16 IN, Overall Length: 9-3/4 IN, Shank Length: 6 IN, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Blade Finish: Nickel-Chrome Plating, Tip Type: Phillips, Shank Size: 3/16 IN
Product Type	Screwdriver, Ideal, Quick-Rotating, PHL Head, 3/16 In Tip, 9-3/4
Special Features	Features: Ideal For Threading Screws In Switches, Fixtures And Anchors; One-Handed Crank Action For Quick And Easy Use; Vapor-Blasted Tip Prevents Plate Chipping; Cross-Ground Tip Provides Precise And Secure Fit In Screw Slot; Nickel-Chrome Plating For Corrosion Resistance; Tough, Chrome Vanadium Steel Shank; Cushioned Rubber Grip; Lifetime Guarantee; Identification Mark On Ends; Shank Size: 3/16 IN

## Manufacturer Information

Brand	Ideal
GTIN	00783250352036
Manufacturers Part Number	35-203
UPC	783250352036

## Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Quick-Rotating, Phillips Head

## Packaging

Carton	1
Weight Per each	0.35

## Uses, Certifications, and Standards

Application	For Threading Screws In Switches, Fixtures And Anchors
-------------	--------------------------------------------------------