

Eaton 36248-4

Catalog Number: 36248-4

Eaton B-Line series wall mounted panel enclosure, 36" height, 8" length, 24" width, NEMA 4, Hinged cover, 4 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	36248-4
	UPC
	782051811605
Product Length/Depth	Product Height
8 in	36 in
Product Width	Product Weight
24 in	63.2 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

Product specifications

Special features

Stainless door clamps

Closure type

Hinged

Finish color

Painted

Color

ANSI 61 gray

Wall thickness

14 gauge

Material

Carbon steel

Mounting method

Wall

Country of origin

US

Cover type

Hinged

Mounting hole details

External mounting feet

Locking provisions

Padlock provision

NEMA Rating

4

Model

4 enclosure

Style

Medium single door

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 36248-4](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)