

Eaton 363012-4

Catalog Number: 363012-4

Eaton B-Line series wall mounted panel enclosure, 36" height, 12" length, 30" width, NEMA 4, Hinged cover, 4 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



General specifications

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton B-Line series wall mounted panel enclosure | 363012-4 |
| | UPC |
| | 782051812701 |
| Product Length/Depth | Product Height |
| 12 in | 36 in |
| Product Width | Product Weight |
| 30 in | 88.7 lb |
| Certifications | |
| UL 50 | |
| CSA C22.2. | |
| NEMA | |

Product specifications

Special features

Stainless door clamps

Closure type

Hinged

Finish color

Painted

Color

ANSI 61 gray

Wall thickness

14 gauge

Material

Carbon steel

Mounting method

Wall

Country of origin

US

Cover type

Hinged

Mounting hole details

External mounting feet

Locking provisions

Padlock provision

NEMA Rating

4

Model

4 enclosure

Style

Medium single door

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 363012-4](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)