



## Stainless Steel Threaded Rod

18-8 & 316 Stainless Steel  
 Stock lengths: 3', 6', 12'

18-8 Stainless Rod Meets ASTM F593 Alloy Group 1  
 316 Stainless Rod Meets ASTM F593 Alloy Group 2

All Stainless Rod Will Meet Minimum Tensile & Yield  
 Requirements Of ASTM F593

### NATIONAL COARSE (USS)

Size	Wt Per 100'	Pieces Per Tube
1/4-20	12.1	50
5/16-18	19.6	35
3/8-16	29.1	25
7/16-14	39.8	17
1/2-13	52.2	12
9/16-12	67.6	10
5/8-11	83.7	8
3/4-10	122.4	5
7/8-9	169.2	4
1-8	220.1	2
1 1/8-7	280.5	1
1 1/4-7	350.0	1
1 3/8-6	417.0	1
1 1/2-6	505.0	1
1 3/4-5	692.0	1
2"-4 1/2	909.0	1
2 1/4"-4 1/2	1166.0	1
2 1/2"-4	1437.6	1
2 3/4"-4	2019.2	Bulk
3"-4	2403.0	Bulk
3 1/4"-4	2820.2	Bulk
3 1/2"-4	3270.8	Bulk
3 3/4"-4	3754.7	Bulk
4"-4	4272.0	Bulk



## Stainless Steel Threaded Rod

18-8 & 316 Stainless Steel

Stock lengths: 3', 6', 12'

18-8 Stainless Rod Meets ASTM F593 Alloy Group 1

316 Stainless Rod Meets ASTM F593 Alloy Group 2

All Stainless Rod Will Meet Minimum Tensile & Yield  
Requirements Of ASTM F593

### NATIONAL COARSE (USS)

Size	Wt Per 100'	Pieces Per Tube
1/4-20	12.1	50
5/16-18	19.6	35
3/8-16	29.1	25
7/16-14	39.8	17
1/2-13	52.2	12
9/16-12	67.6	10
5/8-11	83.7	8
3/4-10	122.4	5
7/8-9	169.2	4
1-8	220.1	2
1 1/8-7	280.5	1
1 1/4-7	350.0	1
1 3/8-6	417.0	1
1 1/2-6	505.0	1
1 3/4-5	692.0	1
2"-4 1/2	909.0	1
2 1/4"-4 1/2	1166.0	1
2 1/2"-4	1437.6	1
2 3/4"-4	2019.2	Bulk
3"-4	2403.0	Bulk
3 1/4"-4	2820.2	Bulk
3 1/2"-4	3270.8	Bulk
3 3/4"-4	3754.7	Bulk
4"-4	4272.0	Bulk