# **T&B° Fittings**

### MC and AC Cable Fittings


Armor-gripping saddle stays open by itself when cable is being inserted!








- · Formed steel body
- · Carefully round bushing





	CABLE OF	CABLE OPENING (IN.)		К.О.	DIMENSIONS (IN.)		
CAT. NO.	MAX.	MIN.	TRADE SIZE	SIZE	A <sup>†</sup>	В	С
3301-TB**	.656	.250	%"	1/2"	31/32	<b>1</b> %6	<b>1</b> ½6
3312-TB	.937	.500	1/2"	1/2"	13/32	1%	13/8
** UL Listed for armo	ored cable only.	UL File No. E	1383		CSA File No.	2884	

TITE-BITE® design holds flexible metal cable firmly in place with a single screw!

### **Adapter** — **EMT** to Flex







**(P** 

(F)

	SIZE	DIMENSIONS (IN.)		
CAT. NO.	FLEX TO EMT	A	В	C
503TB	1/2" - 1/2"	<b>1</b> <sup>21</sup> / <sub>32</sub>	<b>1</b> ¾6	1//8
504	3/4" - 3/4"	<b>1</b> 25/32	<b>1</b> 1/16	21/8
505-TB	1" – 1"	21/32	21/16	25/8
CSA File No. 8004		III. File No. I	F-23018	

Smooth plastic bushing protects conductor insulation from rough edges of armored cable and flexible metal conduit!

#### **Anti-Short Bushing**






CAT. NO.	SIZE (AWG)
390	#14-2, #14-3, #12-2
391	#14-4, #12-3, #6-1, and #4-1
392	#12-4, #10-2, #10-3 and #2-1
393	#10-4, #8-2, #8-3, and #1-1
394	#8-4, #6-2, #6-3, #4-2, #4-3, and #6-4
Colorized.	CSA File No. 589
Temperature Rating: 240° F.	UL not applicable.

## For flexible metal conduit and armored cable.

### **Duplex Clamp Connector**


Malleable iron construction



		DIMENSIONS (IN.)		
CAT. NO.	K.O. SIZE	A	В	
291-TB	1/2"	113/32"	111/16"	
UL File No. E 1383		CSA File No. 2884		

One-piece fitting couples 3/8" flexible metal conduit to 1/2" EMT!

### **Combination Coupling**



	SIZE	DIMENSIONS (IN.)		
CAT. NO.	FLEX TO EMT	A	В	С
449-TB	3/8" - 1/2"	<b>1</b> <sup>21</sup> / <sub>32</sub>	<b>1</b> <sup>1</sup> 1/ <sub>32</sub>	15/16
Cable opening: max656, min250.		UL File No CSA File No		

### Fast and easy installation!

#### Strap

- Elongated bolt hole makes alignment easy, even when holes in mounting surface are off center
- Snap-on design holds strap in place





CAT. NO.	SIZE
65-TB	¾" Flex



